

Digital tuning with presets



All in one CD player with tape deck and digital tuner with 30 preset stations. Plays all CDs including self recorded and is programmable for 20 track replay.

Digital Tuning

- Digital tuning with presets
- Auto store Programming for one-touch radio tuning

Impressive sound

- Dynamic Bass Boost delivers deeper, more dramatic bass
- Bass reflex speakers deliver a powerful, deeper bass

Enjoy favourite music from three different sources

- Player compatible with CD-Recordable and CD-ReWritable
- FM/MW stereo tuner
- Autostop stereo tape deck



PHILIPS

Technical specifications

Sound

- **Loudspeaker enhancement:** Piezo
- **Loudspeaker types:** 2 way bass reflex speaker
- **Sound enhancement:** Dynamic Bass Boost
- **Sound system:** Stereo
- **Speaker diameter:** 4"
- **Output power (RMS):** 2X1.2W
- **Volume Control:** Volume control up / down

Loudspeakers

- **Built-in speakers:** 2
- **Finishing:** Metal
- **Loudspeaker types:** Loudspeakers

Audio Playback

- **Cassette deck technology:** Mechanical
- **Cassette playback modes:** Fast wind / rewind, Full auto stop, Pause key
- **Playback Media:** CD, CD-R, CD-RW
- **Disc playback modes:** Fast forward / backward, Next / previous track search, Repeat play, Shuffle play
- **Loader type:** Top
- **Number of decks:** 1
- **Programmable tracks:** 15

Audio Recording

- **Tape recording enhancement:** CD synchro start recording

Tuner / Reception / Transmission

- **Antenna:** AM antenna, FM antenna
- **Auto digital tuning**
- **Tuner bands:** FM, MW

Convenience

- **Display digits:** 6

Accessories

- **Included accessories:** AC power cord, User manual, Warranty certificate

Dimensions

- **Packaging dimensions (W x H x D):** 470 x 275 x 210 mm
- **Product dimensions (W x H x D):** 400 x 243 x 169 mm
- **Weight:** 2.9 kg
- **Weight incl. packaging:** 3.7 kg

Power

- **Battery type:** LR14
- **Battery voltage:** 1.5 V
- **Mains power**
- **Number of batteries:** 6

Product highlights

Digital tuning with presets

CD-Rewritable Compatible

CD-Rewritable Compatible means that your audio set can play both CD-Recordable (CD-R) and CD-Rewritable (CD-RW) discs. CD-R discs are recordable once and can be played on any audio CD player while CD-RW discs can be recorded and rewritten multiple times and can only be played back on compatible audio CD players. The laser pick-up and CD decoder circuitry of CD-RW compatible players are specially designed to read the special audio CD-RW phase-change recording layer, ensuring you can always play your home-recorded discs on your audio CD system.

Dynamic Bass Boost

Dynamic Bass Boost maximises your music enjoyment by emphasising the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

Auto store programming

Auto store Programming is a convenient feature that allows you to tune in to your favourite stations and set station presets by simply pressing a button. Auto store Programming does away with the hassle of manual radio station tuning and setting of presets. A built-in electrical circuit automatically scans local radio station frequencies, locks on to the strongest radio station signals, and assigns them to specific presets.

Bass reflex speaker system

Bass reflex speaker system delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimise the low frequency roll off of the system. The result is deeper controlled bass and lower distortion. The system works by resonating the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a whole new dimension of deep bass.

FM/MW stereo tuner

Autostop stereo tape deck



Date of issue 2005-12-16

Version: 3.0

12 NC: 9073 101 00554
EAN: 87 10895 75315 9

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.
© 2005 Koninklijke Philips Electronics N.V.
All Rights reserved.
www.philips.com