

Philips  
CD Soundmachine with  
Dynamic Bass Boost



AZ1310

## Digital tuning with presets

All-in-one CD-player with tape deck and digital tuner with 30 preset stations. Plays all CDs including self-recorded and is programmable for 20 track replay.

### Digital Tuning

- Digital tuning with preset stations for extra convenience
- Autostore Programming for one-touch radio tuning

### Impressive sound

- Dynamic Bass Boost for deep and dramatic sound
- Bass Reflex Speaker System delivers a powerful, deeper bass

### Enjoy favorite music from three different sources

- Compatible with CD-Recordable and CD-ReWritable
- FM/MW tuner for radio enjoyment
- Autostop cassette deck

**PHILIPS**

# Specifications

## Sound

- Loudspeaker Enhancement: Piezo
- Loudspeaker types: 2-way Bass Reflex Speaker
- Output power (RMS): 2X1.2W
- Sound Enhancement: Dynamic Bass Boost
- Sound System: Stereo
- Speaker diameter: 4"
- Volume Control: Volume Control up/down

## Loudspeakers

- Built-in speakers: 2
- Finishing: Metal
- Loudspeaker types: Loudspeakers

## Audio Playback

- Cassette Deck Technology: Mechanical
- Cassette Playback Modes: Fast Wind/Rewind, Full Auto Stop, Pause key
- Playback Media: CD, CD-R, CD-RW
- Disc Playback Modes: Fast Forward/Backward, Next/Previous Track Search, Repeat Play, Shuffle Play
- Loader Type: Top
- Number of decks: 1
- Programmable Tracks: 15

## Audio Recording

- Tape Recording Enhancement: CD Synchro Start



## Recording

## Tuner/Reception/Transmission

- Antenna: AM Antenna, FM Antenna
- Auto digital tuning
- Tuner Bands: FM, MW

## Convenience

- Display Digits: 6

## Accessories

- Included accessories: AC Power Cord, User Manual, Warranty certificate

## Dimensions

- Packaging dimensions (W x H x D): 470 x 275 x 210 mm
- Product dimensions (W x H x D): 400 x 243 x 169 mm
- Weight: 2.9 kg
- Weight incl. Packaging: 3.7 kg

## Power

- Battery type: LR14
- Battery voltage: 1.5 V
- Mains power
- Number of batteries: 6

# Highlights

## Digital tuning with presets

Simply tune into the station that you want to preset, press and hold the preset button to memorize the frequency. With preset radio stations that can be stored, you can quickly access your favorite radio station without having to manually tune the frequencies each time.

## Autostore programming

Autostore Programming is a convenient feature that allows you to tune in to your favorite stations and set station presets by simply pressing a button. Autostore Programming does away with the hassle of manual radio station tuning and setting of presets. A built-in electrical circuit automatically scans local radio station frequencies, locks on to the strongest radio station signals, and assigns them to specific presets.

## Dynamic Bass Boost

Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

## Bass Reflex Speaker System

Bass Reflex Speaker System delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimize the low frequency roll-off of the system. The result is deeper controlled bass and lower distortion. The system works by resonating the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a whole new dimension of deep bass.

## CD-R/RW Compatible

CD-Rewritable Compatible means that your audio set can play both CD-Recordable (CD-R) and CD-Rewritable (CD-RW) discs. CD-R discs are recordable once and can be played on any audio CD player while CD-RW discs can be recorded and rewritten multiple times and can only be played back on compatible audio CD players. The laser pick-up and CD decoder circuitry of CD-RW compatible players are specially designed to read the special audio CD-RW phase-change recording layer, ensuring you can always play your home-recorded discs on your audio CD system.

## FM/MW tuner

FM/MW (AM) stereo tuner

## Autostop cassette deck

Autostop cassette deck



Issue date 2015-01-22

Version: 2.0.3

12 NC: 9073 101 00555  
EAN: 87 10895 75316 6

© 2015 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)