

CD sound machine

AZ2010

## CD sound machine

- **Incredible surround**

Feature unique to Philips that creates the illusion of the speakers being much further apart than they actually are, resulting in an enhanced, room-filled stereo effect.

- **Ultrabass**

A technology unique to Philips that provides deep bass sounds previously reproduced only by much bigger loudspeakers.

- **Bass reflex speaker system**

Acoustic system that enhances the upper bass tones to provide a warmer, punchier bass sound.

- **Digital tuner with 29 presets**

Provides fast, accurate tuning to your favourite stations. You can store up to 29 FM and MW stations in memory for fast, easy access.

- **Dynamic bass boost**

- **Compact disc digital audio player**

- **Stereo cassette deck**



**INCREDIBLE  
SURROUND**

**ultrabass**



*Let's make things better*



**PHILIPS**

**Standard product information****Amplifier**

- Output power : 4 W RMS
- Dynamic bass boost
- Ultrabass
- Incredible surround
- Rotary volume control

**Sound system**

- 2 x 4" full range speakers
- Bass reflex speaker system
- Incredible surround
- Metal speaker grilles

**CD player**

- Top loader
- 20 track CD programme and repeat
- CD programme, shuffle and repeat function
- CD synchro start recording
- Search/skip/review

**Cassette deck**

- Single stereo cassette deck
- Normal tape type
- Full automatic stop
- Automatic recording level control

**Tuner**

- Digital tuning
- 29 station presets
- Wavebands /00, /05 : FM stereo/MW/LW
- Frequency ranges : FM 87.5 - 108 MHz
- : MW 525 - 1607 kHz
- : LW 148.5 - 284 kHz
- : AM 503 - 1710 kHz
- Telescopic antenna for FM reception
- Ferroceptor for AM reception

**Display**

- Large LCD display

**Connections**

- Headphone socket : 3.5 mm

**Power supply**

- AC/DC operation
- AC voltage /00, /05 : 230 V, 50 Hz
- Batteries : 6 x 1.5V, R20 cells

**General**

- Material : HIPS/ ABS
- Weight : 4.8 Kg
- Dimensions : 486 mm W x 184 mm H x 280 mm D
- Packaging dimensions : 524 mm W x 244 mm H x 344 mm D
- Quantity /mastercarton : 1

**Product highlights**

- **Compact disc digital audio player**  
Compact disc technology that combines superb digital sound quality with the convenience of random track access and CD functions like CD programme, Shuffle Play and Repeat.
- **20-track programmable**  
Stores up to 20 of your favourite CD tracks for playing back in your order of preference.
- **Shuffle play**  
Plays disc selection randomly, giving you a new sequence of tracks each time.
- **Repeat one/all**  
Repeats the current track, the total CD, or your pre-selected programme.
- **CD next/previous track search**  
Plays the next or previous track at the touch of a button.
- **CD music search**  
Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop.
- **Digital tuner with 29 presets**  
Provides fast, accurate tuning to your favourite stations. You can store up to 29 FM and MW stations in memory for fast, easy access.
- **Stereo cassette deck**  
Play back recorded tapes on this full-functional stereo cassette deck, and record from the built-in CD player or tuner.
- **Full auto stop**  
Automatically shuts off the cassette deck at the end of playback to avoid overstretching the tape.
- **Automatic recording level control**  
Electronic circuit that constantly monitors the input signal to ensure accurate, distortion-free recording.
- **CD synchro start recording**  
Synchronises the start of a recording on audio cassette with the start of a CD at the touch of a button.
- **Bass reflex speaker system**  
Acoustic system that enhances the upper bass tones to provide a warmer, punchier bass sound.
- **Dynamic bass boost**  
Enhances bass tone frequencies to give deep, rich sounds.
- **Incredible surround**  
Feature unique to Philips that creates the illusion of the speakers being much further apart than they actually are, resulting in an enhanced, room-filled stereo effect.
- **Ultrabass**  
A technology unique to Philips that provides deep bass sounds previously reproduced only by much bigger loudspeakers.
- **4" Full-range speakers**  
For excellent sound performance across the entire audio frequency spectrum.
- **Metal mesh speaker grilles**  
Perforated, anodized grilles protect the speaker components.
- **Six-digit multi-functional display**  
Displays CD player information (track, playing time and play modes) and Tuner information (tuned frequency and stereo reception).
- **Stereo headphone socket**  
Enables stereo headphones to be used for private listening pleasure. Automatically switches off speakers when used.
- **AC/DC operation**  
Operates either on batteries or mains supply, using the detachable AC power cord.

1999-01-12  
Printed in Hong Kong  
Subject to modification without notice  
© 1999 Koninklijke Philips Electronics N.V.  
All Rights Reserved

<http://www.philips.com>