






| Model | Features | Speakers | Power | FM | MW | LW | Digital | Other |
|------------|---------------------|------------------|-----------|---------|------------------|--------|---------|---------------|
| AZ 1200/00 | basic | full range 2x 4" | - / x / - | Y / 30W | FM/MW/LW Analog | - | x/- | x / x / x / x |
| AZ 1203/00 | basic digital | full range 2x 4" | - / x / - | Y / 30W | FM/MW/LW Digital | - | x/- | x / x / x / x |
| AZ 1602/00 | double deck | full range 2x 4" | - / x / - | Y / 50W | FM/MW/LW Analog | - | x/- | x / x / x / x |
| AZ 2402/00 | portable micro syst | full range 2x 4" | x / x / - | Y / 30W | FM/MW/LW Digital | - | x/- | x / x / x / x |
| AZ 2407/00 | portable micro syst | full range 2x 4" | x / x / x | Y / 50W | FM/MW/LW Digital | 14-key | x/- | x / x / x / x |
| AZ 2905/00 | portable mini syst | full range 2x 5" | - / x / x | Y / 40W | FM/MW/LW Digital | 23-key | x/x | x / x / x / x |

Subject to modification without notice



Let's make things better.



PHILIPS

