

Portable Micro System with Motorized Tray

- **Compact Disc Digital Audio Player**

Unequaled in accuracy and realism, state-of-the-art compact disc technology is at your fingertips with some of the most sought-after features in the industry.

- **CD Player with Motorized CD Tray**

Loading discs has never been easier thanks to the motorized drawer mechanism. This feature offers the utmost in convenience and safety when handling your valuable collection of CDs.

- **Incredible Surround™**

An exciting, new, psycho-acoustic method of widening the stereo spatial image that expands the sound stage and is especially suited for applications with limited separation of left and right speakers.

- **Digital Sound Control**

DSC offers different sound settings optimized for specific musical styles. Examples are JAZZ, POP, and ROCK settings, each specifically tailored to produce optimum listening pleasure for its corresponding style of music.

- **Digital Tuner with 29 Presets**

Activation of the programming function automatically stores up to 29 AM and FM stations into preset memory locations for fast, easy access.

- **Remote Control**

23-key full digital remote control.



Let's make things better.

PHILIPS **MAGNAVOX**

Standard product information

CD Player

- **Compact Disc Digital Audio Player**

Unequaled in accuracy and realism, state-of-the-art compact disc technology is at your fingertips with some of the most sought-after features in the industry.

- **Motorized CD Tray Loader**

Loading discs has never been easier thanks to the motorized drawer mechanism. This feature offers the utmost in convenience and safety when handling your valuable collection of CDs.

- **Shuffle Play**

Plays all selections on a disc in random order, ignoring the sequential order in which they were originally recorded.

- **Next/Previous Track Search**

This two-button feature offers the opportunity to go back to the previous track or go forward to the next track instantly.

- **Repeat One/All**

Selection of this feature, based on user preference, repeats one track, one disc, or a pre-selected program.

- **CD Synchro Start Recording**

One button allows the cassette deck and CD player to communicate with one another to synchronize the start of a recording on an analog audio cassette deck with the start of a CD or a CD program.

Tuner/Receiver

- **Digital Tuning**

- **29 Radio Presets**

Automatically stores up to 29 AM and FM stations into preset memory locations for fast, easy access.

- **Telescopic FM Antenna**

Adjustable to a variety of lengths this chrome-plated dipole antenna improves FM reception in any location.

- **Ferroceptor AM Antenna**

This built-in ferrite antenna improves portability and surpasses AM reception capabilities of other units not so well equipped.

Cassette

- **Stereo Cassette Deck**

A full function stereo cassette deck permits playback of music from your favorite artists as well as the ability to record from other sources such as CD or AM/FM broadcasts using a simple, easy-to-use mechanical push button assembly.

- **CD Synchro Start Recording**

One button allows the cassette deck and CD player to communicate with one another to synchronize the start of a recording on an analog audio cassette deck with the start of a CD or a CD program.

- **Full Auto Stop**

This feature senses a change in pressure when an audio cassette reaches the end and automatically stops the tape and disengages the transport mechanism.

- **Automatic Recording Level Control**

Micro-electronic circuitry constantly monitors the final audio amplifier stage to ensure accurate, distortion-free recordings every time.

Sound/Speaker

- **Incredible Surround™**

An exciting, new, psycho-acoustic method of widening the stereo spatial image that expands the sound stage and is especially suited for applications with limited separation of left and right speakers.

- **Bass Reflex Speaker System**

Acoustically tuned ports offer increased bass response for richer, fuller low frequency reproduction.

- **Digital Sound Control**

DSC offers different sound settings optimized for specific musical styles. Examples are JAZZ, POP, and DBB settings, each specifically tailored to produce optimum listening pleasure for its corresponding style of music.

- **Digital Up/Down Volume Control**

Convenient and accurate push button volume control without the worry of "scratchy" mechanical controls of the past.

- **Two 4" Full Range Speakers**

For excellent sound reproduction across the entire audio spectrum.

- **Cloth Speaker Grilles**

Cloth covered perforated grilles protect delicate speaker components with smart, high-tech styling.

Additional Features

- **Large Multifunction LCD Display**

This large display is easy to read at any distance with no distortion or distraction and the multi-function format makes it easy to recognize different functions at a glance.

- **Remote Control**

23-key full digital remote control.

- **Stereo Headphone Jack**

Enjoy your favorite CD, cassette, or radio station with full, rich stereo separation without disturbing others.

- **Built-in Carry Handle**

This rugged, integrated handle makes it easy to take your music with you anywhere you go.

- **AC/DC Operation**

For convenience this feature can't be beat. Listen to your favorite artists any time or anywhere using the detachable AC power cord or batteries available at any corner store.

- **Operates on Six D Batteries**

Six D-cell batteries provide hours of uninterrupted music enjoyment anywhere you want to go.

UPC: 037849857205

Product Dimensions: 19.1"W x 9.8"H x 10.8"D

Product Weight: 12 lbs.

Individual Package Dimensions: 18.3"W x 11.9"H x 13.3"D

Individual Package Weight: 14.7 lbs.

Master Pack: 1

Carton Contains: CD AM/FM Stereo Portable Micro System, Multi-Function Remote Control, Two AAA Batteries, AC Cord, Operating Instructions, Warranty Information.

Printed in United States

©1997 Philips Consumer Electronics Co.

A Division of Philips Electronics North America Corp.

Specifications subject to change without notice.

<http://www.philipsmagnavox.com>

Let's make things better.

PHILIPS **MAGNAVOX**