



Philips  
CD Soundmachine with  
Dynamic Bass Boost

AZ3300

## Music on the move

Portable CD player and digital tuner for playing recorded and rewriteable CDs. Designed for worry-free, outdoor use.

### **Designed for motion**

- Fully portable design
- Robust rubber design
- Easy MP3 music navigation via remote control

### **Impressive sound**

- Dynamic Bass Boost for deep and dramatic sound
- Bass Reflex Speaker System delivers a powerful, deeper bass

### **Enjoy digital tuning**

- Digital tuning with preset stations for extra convenience
- Autostore Programming for one-touch radio tuning

# PHILIPS

# Specifications

## Sound

- Output power (RMS): 2X1.6W
- Sound Enhancement: Dynamic Bass Boost
- Sound System: Stereo
- Speaker diameter: 3"
- Volume Control: Volume Control up/down

## Loudspeakers

- Built-in speakers: 2
- Finishing: Metal
- Loudspeaker types: Loudspeakers

## Audio Playback

- Playback Media: CD, CD-R, CD-RW
- Disc Playback Modes: Fast Forward/Backward, Next/Previous Track Search, Repeat Play, Shuffle Play
- Loader Type: Top
- Programmable Tracks: 20

## Tuner/Reception/Transmission

- Antenna: AM Antenna, FM Antenna
- Auto digital tuning
- Station presets: 30
- Tuner Bands: FM, MW



## Convenience

- Display Digits: 6
- Display Type: LCD
- Remote control: 14 keys

## Accessories

- Included accessories: AC Power Cord, User Manual, Warranty certificate
- Remote control: 1

## Dimensions

- Packaging dimensions (W x H x D): 477 x 200 x 310 mm
- Product dimensions (W x H x D): 408 x 155 x 277 mm
- Weight: 2.8 kg
- Weight incl. Packaging: 4.1 kg

## Power

- Battery type: LR14
- Battery voltage: 1.5 V
- Mains power
- Number of batteries: 6

# Highlights

## Fully portable design

Fully portable design

## Robust rubber design

Robust rubber design

## Easy navigation via remote

Easy MP3 music navigation via remote control

## Dynamic Bass Boost

Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

## Bass Reflex Speaker System

Bass Reflex Speaker System delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimize the low frequency roll-off of the system. The result is deeper controlled bass and lower distortion. The system works by resonating the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a whole new dimension of deep bass.

## Digital tuning with presets

Simply tune into the station that you want to preset, press and hold the preset button to memorize the frequency. With preset radio stations that can be stored, you can quickly access your favorite radio station without having to manually tune the frequencies each time.

## Autostore programming

Autostore Programming is a convenient feature that allows you to tune in to your favorite stations and set station presets by simply pressing a button. Autostore Programming does away with the hassle of manual radio station tuning and setting of presets. A built-in electrical circuit automatically scans local radio station frequencies, locks on to the strongest radio station signals, and assigns them to specific presets.



Issue date 2014-02-06

Version: 3.0.4

12 NC: 9073 101 00745  
EAN: 87 10895 77270 9

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)