



Philips
CD Soundmachine with
Dynamic Bass Boost

AZ3300

Music on the move

Portable CD player and digital tuner for playing recorded and rewriteable CDs. Designed for worry free, outdoor use.

Designed for motion

- Fully portable design
- Robust rubber design
- Easy MP3 music navigation via remote control

Impressive sound

- Dynamic Bass Boost for deep and dramatic sound
- Bass Reflex speakers deliver a powerful, deeper bass

Enjoy digital tuning

- Digital tuning with presets
- Autostore Programming for one-touch radio tuning

PHILIPS

Specifications

Sound

- Output power (RMS): 2X1.6W
- Sound Enhancement: Dynamic Bass Boost
- Sound System: Stereo
- Speaker diameter: 3"
- Volume Control: Volume Control up/down

Loudspeakers

- Built-in speakers: 2
- Finishing: Metal
- Loudspeaker types: Loudspeakers

Audio Playback

- Playback Media: CD, CD-R, CD-RW
- Disc Playback Modes: Fast Forward/Reverse, Next/Previous Track Search, Repeat Play, Shuffle Play
- Loader Type: Top
- Programmable Tracks: 20

Tuner/reception/transmission

- Antenna: AM Antenna, FM Antenna
- Auto digital tuning
- Station presets: 30
- Tuner Bands: FM, MW



Convenience

- Display Digits: 6
- Display Type: LCD
- Remote control: 14 keys

Accessories

- Included Accessories: AC Power Lead, User manual, Warranty certificate
- Remote control: 1

Dimensions

- Packaging dimensions (W x H x D): 477 x 200 x 310 mm
- Product dimensions (W x H x D): 408 x 155 x 277 mm
- Weight: 2.8 kg
- Weight incl. Packaging: 4.1 kg

Power

- Battery type: LR14
- Battery voltage: 1.5 V
- Mains power
- Number of batteries: 6

Highlights

Fully portable design

Fully portable design

Robust rubber design

Robust rubber design

Easy navigation via remote

Easy MP3 music navigation via remote control

Dynamic Bass Boost

Dynamic Bass Boost maximises your music enjoyment by emphasising the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

Bass Reflex Speaker System

Bass Reflex Speaker System delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimise the low frequency roll-off of the system. The result is deeper controlled bass and lower distortion. The system works by causing the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a completely new dimension of deep bass.

Digital tuning with presets

Digital tuning with presets

Autostore programming

Autostore Programming is a convenient feature that allows you to tune in to your favourite stations and set station presets by simply pressing a button. Autostore Programming does away with the hassle of manual radio station tuning and setting of presets. A built-in electrical circuit automatically scans local radio station frequencies, locks on to the strongest radio station signals, and assigns them to specific presets.



Issue date 2013-05-10

Version: 3.0.4

12 NC: 9073 101 00745
EAN: 87 10895 77270 9

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com