

Philips  
CD Soundmachine with  
Dynamic Bass Boost



AZ3300

## Music on the move

Portable CD player and digital tuner for playing recorded and rewriteable CDs. Designed for worry-free, outdoor use.

### **Designed for motion**

- Fully portable design
- Robust rubber design
- Easy MP3 music navigation via remote control

### **Impressive sound**

- Dynamic Bass Boost for deep and dramatic sound
- Bass Reflex speakers deliver a powerful, deeper bass

### **Enjoy digital tuning**

- Digital tuning with presets
- Autostore Programming for one-touch radio tuning

**PHILIPS**  
sense and simplicity

# Specifications

## Sound

- Sound Enhancement: Dynamic Bass Boost
- Sound System: Stereo
- Speaker diameter: 3"
- Output power (RMS): 2X1.6W
- Volume Control: Volume Control up/down

## Loudspeakers

- Built-in speakers: 2
- Finishing: Metal
- Loudspeaker types: Loudspeakers

## Audio Playback

- Playback Media: CD, CD-R, CD-RW
- Disc Playback Modes: Fast Forward/Backward, Next/Previous Track Search, Repeat Play, Shuffle Play
- Loader Type: Top
- Programmable Tracks: 20

## Tuner/Reception/Transmission

- Antenna: AM Antenna, FM Antenna
- Auto digital tuning
- Station presets: 30
- Tuner Bands: FM, AM

## Convenience

- Display Digits: 6
- Display Type: LCD
- Remote control: 14 keys

## Accessories

- Included Accessories: AC Power Cord, User Manual, Warranty certificate
- Remote control: 1

## Dimensions

- Packaging dimensions (W x H x D): 477 x 200 x 310 mm
- Product dimensions (W x H x D): 408 x 155 x 277 mm
- Weight: 2.8 kg
- Weight incl. Packaging: 4.1 kg

## Power

- Battery type: LR14
- Battery voltage: 1.5 V
- Mains power
- Number of batteries: 6



# Highlights

## Fully portable design

Fully portable design

## Robust rubber design

Robust rubber design

## Easy navigation via remote

Easy MP3 music navigation via remote control

## Dynamic Bass Boost



Dynamic bass boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

## Bass Reflex Speaker System

Bass Reflex Speaker System delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimize the low frequency roll-off of the system. The result is deeper controlled bass and lower distortion. The system works by resonating the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a whole new dimension of deep bass.

## Digital tuning with presets

Digital tuning with presets

## Autostore programming

Autostore Programming is a convenient feature that allows you to tune in to your favorite stations and set station presets by simply pressing a button. Autostore Programming does away with the hassle of manual radio station tuning and setting of presets. A built-in electrical circuit automatically scans local radio station frequencies, locks on to the strongest radio station signals, and assigns them to specific presets.

