

## Ultra-Compact CD Player with 25-second ESA

- **Electronic Shock Absorption**

Automatically stores 25 seconds of music during play to prevent interruptions caused by vibrations and shocks.

- **Ultra-Compact Design**

Advanced micro-electronic circuitry for portability and outstanding performance, with innovative styling in a superb design.

- **3-Stage Dynamic Bass Boost**

Enhances bass tone frequencies to give three levels of deep, rich sounds.

- **Extended Playing Time**

Innovative, power-saving technology extends battery playing time to 12 hours (2 "AA" batteries).

- **Other CD Features Include:**

Large LCD, 99-track programming, shuffle, repeat one/all and introscan functions, and feedback beep to confirm key-push operation.

- **Headphone, AC/DC Adaptor, Hifi Cord, Pouch and NiCad Batteries Included**



## Standard product information

### Amplifier/System

- Output power (headphone) 2 x 12 mW RMS
- 3-stage Dynamic Bass Boost
- Automatic power switch-off
- Rotary volume control
- Built-in battery recharger function for NiCad battery
- Acoustic feedback

### CD Player

- Electronic Shock Absorption (ESA) with 25-second memory
- 99-track programmable, shuffle, repeat 1/all and introscan
- Search forward/backward with sound
- 1-Bit D/A converter for pure sound reproduction
- S/N ratio (A weighted) : > 85 dB
- Frequency response : 20 Hz - 20 kHz.
- Resume and hold

### Display

- 6-digit LCD
- Indications for track, time, DBB, CD functions, battery and ESA

### Connections

- Headphone/line out : stereo, 3.5 mm
- DC in : 4 mm, 4.5 V, centre '+'

### Power Supply

- Batteries : 2 x 1.5 V, type AA/LR6/UM3 cell
- Typical playing time : 12 hours
- External supply /01, /11 : 120/230 V AC (switchable) to 4.5 V DC

### General

- Material : High temperature resistant plastic
- Weight : 230 g (excluding batteries)
- Dimensions : 128 mm W x 28 mm H x 136.5 mm D
- Quantity/mastercarton : 3

### Accessories

- AC/DC adaptor
- Stereo in-ear headphone
- Rechargeable battery pack
- Hifi cord
- Pouch

### Optional Accessories (contact your dealer or service centre)

- AY 3500 : Car cassette adaptor (for logic decks)
- AY 3501 : Car cassette adaptor
- AY 3545 : Cigarette lighter adaptor

## Product Highlights

### • Large LCD

Large LCD ensures that all CD function displays are bigger and brighter for easier viewing.

### • Feedback Tone

Confirms any key-push with friendly beep.

### • Play Mode

Let's you enjoy various track repeat modes (one/all/shuffle) or a combination of each. Introscan plays 8 seconds of each track automatically.

### • Next/Previous Track Search

Two-button control that puts you immediately at the start of the previous track or next track.

### • Search With Sound

Produces audible "bits" of sound while you search backwards or forwards within a CD track.

### • Hold

Prevents accidental interruption of play or changing of the setting.

### • Resume

Ensures the CD starts precisely from the point it was stopped.

### • Automatic Power Off

Automatically switches off the CD player at the end of a compact disc.

### • Scratch Resistant

Advanced in-mould foil technology provides the CD player with a durable, scratch-resistant surface.

### • 1-Bit D/A Converter

Advanced digital conversion technology ensures crystal-clear sounds for pure listening pleasure.

### • Stereo In-Ear Headphone

Stylish, ergonomically designed in-ear headphone for exceptionally snug fit and outstanding sound quality.

### • Heat Resistant Body

Unique plastic composition enables the CD player to withstand very high temperatures while protecting the internal components.