

CD portable

AZ7680

Ultra-compact CD player with Dynamic bass boost

- **Ultra-compact design**

Advanced micro-electronic circuitry for portability and outstanding performance, with innovative styling in a superb design.

- **CD-Rewritable compatible**

This ultra-compact CD player is capable of playing both CD-recordable and CD-Rewritable disks.

- **Dynamic bass boost**

Enhances bass tones to give deep, rich sounds.

- **Extended playing time**

Innovative, power-saving technology extends battery playing time to 15 hours (2 'AA' batteries).

- **Other CD features include:**

15-track programming, shuffle, repeat one/all and introscan functions, and feedback beep to confirm key-push operation.

- **Headphone included**



Let's make things better.



PHILIPS

CD portable

AZ7680

Standard product information

Amplifier/system

- Output power (headphone) 2 x 12 mW RMS
- Dynamic bass boost
- Automatic power switch-off
- Rotary volume control
- Built-in battery recharge function for NiCad packs
- Acoustic feedback

CD player

- 15-track programmable, shuffle, repeat 1/all and introscan
- Search forward/backward with sound
- Dual D/A convertor with very low distortion
- S/N ratio (A weighted) : > 100 dB
- Frequency response : 20 Hz - 20 kHz.
- Resume and hold

Display

- 6-digit LCD
- Indications for track, time, battery and CD functions

Connections

- Headphone/line out : stereo, 3.5 mm
- DC in : 4.0 mm, 4.5 V, centre '+'

Power supply

- Batteries : 2 x 1.5 V, type AA/LR6/UM3 cell
- Typical playing time : 15 hours
- External supply /00 : 230 V AC to 4.5 V DC
- /01, /11 : 120/230 V AC (switchable) to 4.5 V DC

General

- Material : High temperature resistant plastic
- Weight : 230 g (excluding batteries)
- Dimensions : 128 mm W x 27.5 mm H x 136.5 mm D
- Quantity/mastercarton : 6

Accessories

- Stereo in-ear headphone

Optional accessories (contact your dealer or service centre)

- AY 3160 : AC/DC adaptor
- AY 3501 : Car cassette adaptor
- AY 3545 : Cigarette lighter adaptor
- AY 3361 : Rechargeable NiCad battery pack

Product highlights

- **Feedback tone**
Confirms any key-push with friendly beep.
- **Play mode**
Let's you enjoy various track repeat modes (one/all/shuffle) or a combination of each. Introscan plays 8 seconds of each track automatically.
- **Next/previous track search**
Two-button control that puts you immediately at the start of the previous track or next track.
- **Search with sound**
Produces audible 'bits' of sound while you search backwards or forwards within a CD track.
- **Hold**
Prevents accidental interruption of play or changing of the setting.
- **Resume**
Ensures the CD starts precisely from the point it was stopped.
- **Automatic power off**
Automatically switches off the CD player at the end of a compact disc.
- **Heat resistant body**
Unique plastic composition enables the CD player to withstand very high temperatures while protecting the internal components.
- **Stereo in-ear headphone**
Stylish, ergonomically designed in-ear headphone for exceptionally snug fit and outstanding sound quality.

1999-01-06
Printed in Hong Kong
Subject to modification without notice
© 1998 Koninklijke Philips Electronics N.V.
All Rights Reserved

<http://www.philips.com>

Let's make things better.



PHILIPS