



Philips  
CD Soundmachine

CD, MP3-CD, USB, FM

Tape  
Remote Control  
12W

AZ787

## Powerful portable sound

with 12W RMS total output power

Enjoy digital music from your portable device in powerful sound on the Philips CD soundmachine - anytime, anywhere. Thanks to USB Direct, Bass Reflex Speakers and 12W RMS total output power.

### Easy to use

- Handy remote control for extra convenience
- Sleep timer for easy falling asleep to your favorite music
- Stereo headphone jack for better personal music enjoyment

### Powerful sound you can hear and feel

- Dynamic Bass Boost for deep and dramatic sound
- Digital Sound Control for optimized music style settings
- Bass Reflex Speaker System delivers a powerful, deeper bass

### Enjoy your music from multiple sources

- Play MP3/WMA-CD, CD and CD-RW
- USB Direct for MP3/WMA music playback
- Digital tuning with preset stations for extra convenience
- Autostop cassette deck
- Audio-in for easy portable music playback

# PHILIPS

# Highlights

## USB Direct



With the USB Direct mode, simply plug in your USB device to the USB port on your Philips device and your digital music will be played directly from the Philips device.

## Play MP3/WMA-CD, CD and CD-RW



Audio compression technology allows large digital music files to be reduced up to 10 times in size without radically degrading their audio quality. MP3 or WMA are two of the compression formats that let you enjoy a world of digital music on your Philips player. Download MP3 or WMA songs from authorized music sites on the Internet or create your own MP3 or WMA music files by ripping your audio CDs and transferring them onto your player.

## Bass Reflex Speaker System



Bass Reflex Speaker System delivers a deep bass experience from a compact loudspeaker box system. It differs from a conventional loudspeaker box system in the addition of a bass pipe that is acoustically aligned to the woofer to optimize the low frequency roll-off of the system. The result is deeper controlled bass and lower distortion. The system works by resonating the air mass in the bass pipe to vibrate like a conventional woofer. Combined with the response of the woofer, the system extends the overall low frequency sounds to create a whole new dimension of deep bass.

## Handy remote control



With a handy remote control for greater convenience at your fingertips, all you have to do is sit back and relax.

## Stereo headphone jack

Connect your own headphones with this Philips device for a more personal listening experience whenever you want it. You can

enjoy your favorite music in great sound without disturbing others by connecting your headphones to this device.

## Dynamic Bass Boost



Dynamic Bass Boost maximizes your music enjoyment by emphasizing the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.

## Digital tuning with presets



Simply tune into the station that you want to preset, press and hold the preset button to memorize the frequency. With preset radio stations that can be stored, you can quickly access your favorite radio station without having to manually tune the frequencies each time.



# Specifications

## Audio playback

- Disc playback modes: fast forward/backward, next/previous track search, repeat/shuffle/program
- Playback media: CD, CD-R, CD-RW, MP3-CD, WMA-CD
- USB Direct playback modes: fast backward/fast forward, previous/next, program play, shuffle, play/pause, repeat, stop
- Number of decks: 1
- Cassette deck technology: mechanical

## Tuner/Reception/Transmission

- Antenna: FM antenna
- Station presets: 20
- Tuner bands: FM
- Tuner enhancement: auto digital tuning

## Sound

- Volume control: rotary (digital)
- Sound system: stereo
- Sound enhancement: Dynamic Bass Boost 2 steps
- Maximum output power (RMS): 12W

## Loudspeakers

- No. of built-in speakers: 2
- Speaker grille finishing: metal
- Loudspeaker enhancement: 2-way bass reflex speaker

## Connectivity

- USB: USB host
- Audio/Video output: Headphone (3.5mm)
- Audio in (3.5mm)

## Convenience

- Loader type: top
- Display type: LCD display with backlight

## Power

- Number of batteries: 6 x LR20 for main set (not included), 1x CR2025 for RC (included)
- Power type: 220 - 240V

## Accessories

- Remote control
- Quick start guide: multi-languages
- Power cord
- Warranty: Warranty leaflet

## Dimensions

- Product weight: 3 kg
- Weight incl. Packaging: 4 kg
- Packaging dimensions (WxDxH): 468 x 198 x 310 mm
- Product dimensions (WxDxH): 435 x 270 x 170 mm



Issue date 2019-07-04

Version: 1.0.2

12 NC: 8670 001 59653  
EAN: 69 51613 99773 4

© 2019 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* Avoid extensive use of the set in a volume higher than 85 decibel  
because this may damage your hearing.