

Ultra-compact CD Portable

- **Digital dynamic bass boost**

Enhances bass at low, mid and high volume, to give deep, rich sounds.

- **Extended playing time up to 18 hours**

Powersaving technology extends battery playing time to 18 hours with two regular LR6-size (AA) alkaline batteries.

- **CD-Rewritable compatible**

Ensures that both CD-Recordable and CD-Rewritable disks, made by any CD-Recorder, can be played.

- **All CD program modes**

Let's you enjoy various CD program modes (repeat one/ repeat all / shuffle/ introscan). Introscan plays 8 seconds of each track automatically to quickly scan a CD.

- **Headphone and AC/DC adapter included**



Standard product information

Amplifier/ system

- Output power (in-ear headphone) 2 x 3mW RMS
- 1-Bit D/A convertor for pure sound reproduction
- Digital dynamic bass boost
- Rotary volume control
- S/N ratio (A weighted) : >100 dB
- Frequency response : 20 Hz - 20 kHz
- Acoustic feedback

CD player

- 15-Track programmable, shuffle, repeat 1/ all and introscan
- Search forward/ backward with sound
- Resume and hold

LCD display

- Indications for track, time, DBB, CD functions and battery status

Connections

- Headphone/line out : stereo, 3.5 mm
- DC in : 4.0 mm, 4.5V, centre '+'

Power supply

- Batteries : 2 x 1.5V, type AA/LR6/UM3 cell
- Battery playing time : 18 hours (regular AA size, alkaline batteries)
- Automatic power switch-off

General

- Material : High temperature resistant plastic
- Weight : 230 g (excluding batteries)
- Product dimensions : 128 mm W x 28 mm H x 138 mm D
- D-box dimensions /00, /09, /10, /13 : 245 mm L x 146 mm W x 49 mm H
- D-box dimensions /01, /05, /11, /16 : 256 mm L x 145 mm W x 54 mm H
- Master carton dimensions /00, /09, /10, /13 : 350 mm L x 299 mm W x 199 mm H
- Master carton dimensions /01, /05, /11, /16 : 381 mm L x 303 mm W x 199 mm H
- Master carton quantity : 6

Accessories

- AC/DC adapter
- Stereo in-ear headphone

Optional accessories (contact your dealer or service center)

- AY3501 : Car cassette adapter
- AY3545 : 4.5V Car cigarette lighter DC/DC adapter

Power supply adapter

- /00, /05, /09 : 230V/50Hz to 4.5V
- /01, /11, /16 : 120/230V 50/60Hz (switchable) to 4.5V
- /13 : 230V/60Hz to 4.5V

Product highlights

- **Compact disc audio player**
Compact Disc technology that provides uncompressed superb digital sound quality.
- **Heat resistant body**
Unique composite material enables the CD player to withstand very high temperatures for in-car use.
- **1-Bit D/A converter**
Advanced digital conversion technology ensures crystal-clear sound.
- **Hold**
Locks all buttons electronically to prevent interruption of play or change of program settings.
- **Resume**
Ensures the CD starts precisely from the point it was stopped.
- **Automatic power off**
Automatically switches off the CD player at the end of a compact disc.
- **CD next/ previous**
Plays the next or previous track at the touch of a button
- **CD music search**
Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop
- **Repeat one/ all**
Repeat the current track or the total CD
- **Shuffle**
Plays disc selection randomly, giving you each time a new sequence of tracks
- **15-track programmable**
Stores up to 15 of your favourite tracks for playing back in your order of preference
- **Acoustic feedback**
Confirms any key-push with friendly beep to acknowledges that a command has been given.

1999-09-20
Printed in Hong Kong
Subject to modification without notice
© 1999 Royal Philips Electronics
All Rights Reserved.

<http://www.philips.com>

Let's make things better.



PHILIPS