

Shockproof CD player with powersaving 45-second ESP³

- **Powersaving Electronic skip protection**

Automatically stores 45 seconds of music to prevent music interruptions caused by shocks. Powersaving ESP³ improves battery performance compared to ESP off.

- **Digital dynamic bass boost**

Enhances bass at low, mid and high volume, to give deep, rich sounds.

- **Extended playing time up to 20 hours**

Powersaving technology extends battery playing time to 20 hours with two regular LR6-size (AA) alkaline batteries (ESP³ on).

- **CD-Rewritable compatible**

Ensures that both CD-Recordable and CD-Rewritable disks, made by any CD-Recorder, can be played.

- **All CD program modes**

Let's you enjoy various CD program modes (repeat one/ repeat all / shuffle/ introscan). Introscan plays 8 seconds of each track automatically to quickly scan a CD.

- **Headphone and AC/DC adapter included**



Standard product information

Amplifier/ system

- Output power (in-ear headphone) 2 x 3mW RMS
- 1-Bit D/A convertor for pure sound reproduction
- Digital dynamic bass boost
- Rotary volume control
- S/N ratio (A weighted) : >100 dB
- Frequency response : 20 Hz - 20 kHz
- Acoustic feedback

CD player

- 99-Track programmable, shuffle, repeat 1/ all and introscan
- Search forward/ backward with sound
- Resume and hold

ESP - Electronic skip protection

- Electronic skip protection with 45 second memory

LCD display

- Indications for track, time, DBB, CD functions, ESP and battery status

Connections

- Headphone/ line out : stereo, 3.5 mm
- DC in : 4.0 mm, 4.5V, centre '+'

Power supply

- Batteries : 2 x 1.5V, type AA/LR6/UM3 cell
- Battery playing time : 20 hours (Alkaline)
- Automatic power switch-off

General

- Material : High temperature resistant plastic
- Weight : 230 g (excluding batteries)
- Product dimensions : 128 mm W x 28 mm H x 138 mm D
- D-box dimensions : 256 mm L x 145 mm W x 54 mm H
- Master carton dimensions : 303 mm L x 210 mm W x 199 mm H
- Quantity/mastercarton : 3

Accessories

- Stereo in-ear headphone
- AC/DC adapter

Optional accessories (contact your dealer or service center)

- AY3501 : Car cassette adapter
- AY3545 : 4.5V Car cigarette lighter DC/DC adapter

Power supply adapter

- /00 : 230V/50Hz to 4.5V
- /01 : 120/230V 50/60Hz (switchable) to 4.5V

Product highlights

• Compact disc audio player

Compact Disc technology that provides uncompressed superb digital sound quality.

• Heat resistant body

Unique composite material enables the CD player to withstand very high temperatures for in-car use.

• 1-Bit D/A converter

Advanced digital conversion technology ensures crystal-clear sound.

• Hold

Locks all buttons electronically to prevent interruption of play or change of program settings.

• Resume

Ensures the CD starts precisely from the point it was stopped.

• Automatic power off

Automatically switches off the CD player at the end of a compact disc.

• CD next/ previous

Plays the next or previous track at the touch of a button

• CD music search

Searches the CD at high speed while still producing low-volume sound so you know exactly when to stop

• Repeat one/ all

Repeat the current track or the total CD

• Shuffle

Plays disc selection randomly, giving you each time a new sequence of tracks

• 99-track programmable

Stores up to 99 of your favourite tracks for playing back in your order of preference

• Acoustic feedback

Confirms any key-push with friendly beep to acknowledges that a command has been given.