

Philips
LCD monitor

23" / 58.4cm
Autostereoscopic 3D
Full HD

BDL2331VS



A full 3D experience

without the need for special glasses

Deliver your messages in stunning 3D, with excellent picture quality and no need for special glasses. With 28 lenticular views you can deliver jaw dropping images that will amaze your audience.

Operational flexibility

- Autostereoscopic 3D

Stunning 3D experience

- 2D plus depth
- 28 lenticular views for amazing smooth 3D pictures
- 3D content visualization

Optimized for public viewing

- Full HD LCD display, 1920x1080p

Lower total cost of ownership

- SmartPower for energy saving

Sustainable and safe

- Temperature sensor measures the health condition
- Complies with RoHS standards to care for the environment

PHILIPS

Specifications

Picture/Display

- Diagonal screen size: 23 inch / 58.9 cm
- Panel resolution: 1920x1080p
- Optimum resolution: 1920 x 1080 @ 60Hz
- Brightness: 300 cd/m²
- Contrast ratio (typical): 1000:1
- Response time (typical): 5 ms
- Aspect ratio: 16:9
- Viewing angle (H / V): 150 / 150 degree
- Pixel pitch: 0.265 x 0.265 mm
- Display colors: 16.7 million colors
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, Progressive scan, 3D MA deinterlacing, Dynamic contrast enhancement
- 3D Technology: Autostereoscopic 3D display, Fixed Lenticular 3D Technology, Input Format: 2D plus depth

Connectivity

- PC: DVI-D x1
- AV output: Audio (L/R) x1
- USB: USB 2.0 x 1

Convenience

- Placement: Landscape
- Screen saving functions: Pixel shift, Low bright
- Keyboard control: Hidden, Lockable
- Energy saving functions: Ambient light sensor, Smart Power
- Safety control functions: Heat Control, Temperature Sensor
- Picture performance: Advanced color control
- Packaging: Reusable box

Dimensions

- Bezel thickness: 1.6 cm / 0.63 inch
- Set dimensions (W x H x D): 566 x 360 x 50 mm
- Set dimensions with stand (H x D): 499 x 171 mm
- VESA Mount: 100 x 100 mm
- Product weight: 6.5 kg
- Product weight (lb): 14.3

Operating conditions

- Temperature range (operation): 0 - 40 °C
- Relative humidity: 20 - 80 %
- MTBF: 50.000 hour(s)

Power

- Consumption (On mode): Typ. 28.62W
- Standby power consumption: 0.1W

Sound

- Built-in speakers: 2 x 1.5 W

Accessories

- Included accessories: Remote Control, Batteries for remote control, AC Power Cord, User manual on CD-ROM, Quick start guide
- Optional accessories: 3D rendering box

Miscellaneous

- On-Screen Display Languages: English, French, German, Italian, Polish, Turkish, Russian, Simplified Chinese
- Regulatory approvals: CE, RoHS, GOST
- Warranty: Europe/North America: 1 year

Highlights

Autostereoscopic 3D

Enjoy a stunning 3D experience with no need for special glasses thanks to the autostereoscopic 3D effect. Using lenticular technology, it gives excellent clarity and depth, making your 3D experience even more lifelike and enjoyable.

Full HD LCD display 1920x1080p

This display has a resolution that is referred to as Full HD. The state-of-the-art LCD screen technology has the full high-definition widescreen resolution of 1080 progressive lines, each with 1920 pixels. This allows the best possible picture quality for HD input signals with up to 1080 lines. It produces brilliant flicker-free progressive scan pictures with optimum brightness and superb colors. This vibrant and sharp image will provide you with an enhanced viewing experience.

SmartPower

The backlight intensity can be controlled and pre-set by the system to reduce the power consumption by up to 50%, which saves substantially on energy costs.

Temperature sensor

This public display contains a temperature sensor to monitor the internal health condition. In case the internal temperature surpasses the preset threshold, automatically two internal fans will be activated to cool down the display to normal conditions.

Compliant with RoHS standards

Philips designs and produces display products in compliance with strict Restriction of Hazardous Substances (RoHS) standards that restrict lead and other toxic substances that can harm the environment.

28 lenticular views

With 28 lenticular views, you can "peek" around virtual objects on the 3D display, giving you the most stunning 3D visual effects around.

2D plus depth

2D-plus-Depth converted to 28 different views and interwoven into a stunning 3D format

3D content visualization

Software tools are provided with the display to play-out 3D content and control the 3D and 2D visualization parameters. The actual 3D content can be created via plug-ins available for popular 3D animation software packages. Existing 2D or stereo content can be converted into 2D-plus-Depth format. The 2D-plus-Depth format is compatible with existing compression tools, as the additional bandwidth of the depth is small.



Issue date 2022-04-21

Version: 1.2.1

12 NC: 8670 000 87691
EAN: 87 12581 63767 5

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com