



Philips Signage Solutions  
E-Line Display

47"

Edge LED Backlight  
Full HD

**Signage**Solutions

BDL4765EL

## Connect with your audience 24/7

With the future proof Smart Collection

With this ultra slim Signage Solution display, you will enjoy all the benefits of state-of-the-art connectivity and content management possibilities while being ensured that remote management safeguards the lowest cost of ownership.

### **Optimized for public viewing**

- Full HD LED technology for brilliant images
- IPS wide view technology for image and color accuracy
- Designed for 24/7 operation

### **Care about you, your business and your audience**

- Keep your content up and running with FailOver
- SmartPower for energy saving

### **Innovative solutions for any signage application**

- Free and easy-to-use content management with SmartCMS
- Connect and control your content via the cloud with HTML5
- Schedule what you want, when you want with SmartPlayer
- Optional OPS Slot
- Connect your display and start sharing with DLNA

### **Maximizing the impact of your message**

- Manage and control your network remotely via SmartControl

# PHILIPS

# Highlights

## Full HD LED technology

White LED's are solid state devices which light up to full, consistent brightness faster saving startup time. LED's are free from mercury content which allows for eco-friendly recycling and disposal process. LED's allow for better dimming control of LCD backlight, resulting in super high contrast ratio. It also gives superior color reproduction thanks to consistent brightness across the screen.

## IPS Display Technology


Philips IPS displays uses an advanced technology which gives you extra wide viewing angles of 178/178 degree, making it possible to view the display from almost any angle - even in portrait mode. IPS displays gives you remarkably crisp images with vivid colors, especially suitable for professional video wall and menuboard applications which demand color accuracy and consistent brightness at all times.

## SmartControl



SmartControl lets you remotely control and manage your network of displays via RJ45 and RS232C. Easily fine-tune all display settings including resolution, brightness, contrast and cloning of your settings over your complete network.

## SmartCMS



Free and easy-to-use content management system that works exclusively with Philips Sigage Solutions displays to manage your digital signage content. With SmartCMS you can create and schedule your own content over 24 hours every day. Simply create your network, design your content, schedule your playlist and you are ready to play!

## Integrated HTML5 browser



Connect and control your content via the cloud with the integrated HTML5 browser. Design your signage content online and connect it with a display or with your complete network. Simply plug in a RJ45 internet cable for network connection, connect the display with the dedicated url-address and you are ready to play your cloud based content.

## FailOver

Keeping your content up and running is critical for demanding commercial applications. While it is unlikely you will face a content disaster, FailOver provides 24/7 protection with a revolutionary technology that plays back-up content on screen in the event of a media player failure. FailOver automatically kicks in when the primary input fails. Simply select a primary input connection and a FailOver connection and your ready for instant protection.

## SmartPlayer



Turn your USB into a true cost effective digital signage device. Simply save your content (video, audio, pictures) on your USB and plug into your display. Create your playlist and schedule your content via the on screen menu, and enjoy your own created playlists anytime, anywhere.

## Optional OPS Slot

Open Pluggable Specification is an industry standard slot in which you can add an OPS-compatible media player. This gives you the ability to upgrade or change your hardware whenever you need. Turning your display in to an all-in-one digital signage solution has become simplicity personified.

## SmartPower

The backlight intensity can be controlled and pre-set by the system to reduce the power consumption by up to 50%, which saves substantially on energy costs.

## Designed for 24/7 operation

Because business never sleeps, our signage displays are designed for 24/7 use. Taking advantage of superior components to ensure a higher level of quality, you can count on this range of models for complete around-the-clock reliability.

## Share & Stream with DLNA

Simply share & stream content from your mobile device or media player to your display with all DLNA compliant media devices. Connect each display with an ethernet cable and manage your content real time within your local network. Simply connect your display and start sharing.

# Specifications

## Picture/Display

- Diagonal screen size: 47 inch / 119.3 cm
- Panel resolution: 1920x1080p
- Optimum resolution: 1920 x 1080 @ 60Hz
- Brightness: 500 cd/m<sup>2</sup>
- Contrast ratio (typical): 1400:1
- Dynamic contrast ratio: 500,000:1
- Aspect ratio: 16:9
- Response time (typical): 12 ms
- Display colors: 1073.7 million
- Viewing angle (H / V): 178 / 178 degree
- Picture enhancement: 3/2 - 2/2 motion pull down, 3D Combfilter, Motion compens. deinterlacing, Progressive scan, 3D MA deinterlacing, Dynamic contrast enhancement

## Connectivity

- Video input: DisplayPort (1.2), HDMI (x2), DVI-D, VGA (Analog D-Sub), USB, Component (BNC x3), Composite (BNC)
- Video output: DisplayPort, DVI-I, VGA (Analog D-Sub)
- Audio input: Audio Left/Right (RCA), 3.5 mm jack
- Audio output: Audio Left/Right (RCA), External speaker connector
- Other connections: OPS
- External control: RJ45, RS232C (in/out) 2.5 mm jack, IR (in/out) 3.5 mm jack

## Supported Display Resolution

### • Computer formats

| Resolution  | Refresh rate     |
|-------------|------------------|
| 1920 x 1200 | 60Hz             |
| 1920 x 1080 | 60Hz             |
| 1600 x 1200 | 60Hz             |
| 1440 x 900  | 60Hz             |
| 1366 x 768  | 60Hz             |
| 1360 x 768  | 60Hz             |
| 1280 x 1024 | 60Hz             |
| 1280 x 800  | 60Hz             |
| 1280 x 768  | 60Hz             |
| 1024 x 768  | 60Hz             |
| 800 x 600   | 60, 72, 75Hz     |
| 640 x 480   | 60, 67, 72, 75Hz |

### • Video formats

| Resolution | Refresh rate |
|------------|--------------|
| 1080p      | 50, 60Hz     |
| 1080i      | 50, 60Hz     |
| 720p       | 50, 60Hz     |
| 576i       | 50Hz         |
| 576p       | 50Hz         |
| 480p       | 60Hz         |
| 480i       | 60Hz         |

## Dimensions

- Bezel width: 9.9 mm
- Set dimensions (W x H x D): 1068.6 x 612.8 x 54.9 mm

- Product weight: 18.2 kg
- VESA Mount: 400 x 400 mm
- Smart Insert mount: 100 x 100 mm, 100 x 200 mm

## Convenience

- Placement: Landscape, Portrait
- Tiled Matrix: Up to 10 x 10
- Keyboard control: Hidden, Lockable
- Signal Loop Through: DVI, VGA, RS232, DisplayPort, IR Loophthrough
- Network controllable: RJ45, RS232, HDMI (One Wire), One Wire (HDMI-CEC), Card OPS RS232
- Energy saving functions: Smart Power
- Ease of installation: Smart Insert, AC Out
- Screen saving functions: Pixel Shift, Low Bright
- Other convenience: Carrying handles

## Power

- Consumption (On mode): 85.51 W (EnergyStar 6.0 test method)
- Standby power consumption: <0.3 W
- Mains power: 100 ~ 240 VAC, 50 ~ 60 Hz

## Operating conditions

- Temperature range (operation): 5 ~ 35 °C
- Temperature range (storage): -20 ~ 60 °C
- Relative humidity: 20 ~ 80 %
- MTBF: 60,000 hour(s)
- Altitude: 0 ~ 3000 m

## Sound

- Built-in speakers: 2 x 10 W RMS

## Multimedia Applications

- USB Playback Audio: AAC, AIF, AIFF, ASF, LPCM, M3U, M4A, MP3, MP4, WAV, WMA
- USB Playback Picture: BMP, GIF, JPEG, JPG
- USB Playback Video: M2TS, M4V, MK3D, MKV, MP4, MPEG, MPG, MTS, TS, TTS, VOB, WMV

## Accessories

- Included accessories: Remote Control, Batteries for remote control, AC Power Cord, RS232 cable, VGA cable, User manual on CD-ROM, Quick start guide
- Stand: BM05462 (Optional)
- Optional accessories: ColourCalibrationKit (CCK4601), HDBaseT OPS Receiver (CRD25)

## Miscellaneous

- On-Screen Display Languages: English, French, German, Spanish, Polish, Italian, Turkish, Russian, Simplified Chinese, Traditional Chinese, Arabic, Japanese
- Regulatory approvals: CE, FCC, Class B, UL/cUL, CCC, C-Tick, RoHS, GOST, BSMI, CB, J-Moss, PSE, VCCI
- Warranty: 3 year warranty



Issue date 2015-07-15

Version: 5.1.1

12 NC: 8670 001 13721  
EAN: 87 12581 71783 4

© 2015 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)