



Philips LED Bike lights
Saferide

80 LUX

Battery driven
Black aluminium



BF48L20BBLX1

Feel safe, ride safe

High performance battery front Bikelight

Empower yourself on the road with the Saferide LED Bikelight 80 battery-driven motorcycle-like performance. With a specially crafted retro reflector and unique housing design.

Extra wide illumination

- Motorcycle performance: up to 60 metres road illumination
- High efficiency reflector
- Foreground illumination
- Glare free beam
- Legally approved according to StZVO in Germany

Robust

- Long life LED technology
- Waterproof aluminium housing

Seven times more light

- 220 lumen in the beam
- Crystal white light (5500 K)

7x more light

- Powered by 2 new generation High-power Luxeon LEDs (80 lux)
- New generation of high-power Luxeon LEDs

PHILIPS

Saferide
80 LUX Battery driven, Black aluminium

Highlights

Powered by 2 Luxeon LED



Powered by 2 new generation High-power Luxeon LEDs (80 lux). These high quality LEDs have been designed for the automotive industry and are now available to provide safety for bikers on the road.

New generation of LED



To ensure best visibility, our bikelights come equipped with high-power Luxeon LEDs. These high quality LEDs have been designed for the automotive industry and are now available to provide safety for bikers on the road.

Lighting performance

220 lumen in the beam

Motorcycle performance



Standard 10 lux

Philips Saferide 80 lux

Motorcycle performance: up to 60 metres homogeneous road illumination

Waterproof aluminium housing

Waterproof aluminium housing

Long life LED technology




Long life LED technology

Light temperature

Crystal white light (5500 K)

Foreground illumination



Foreground illumination

Glare free beam



Glare free beam

High efficiency reflector

High efficiency reflector

Legally approved

Legally approved according to StZVO in Germany

BF48L20BBLX1

Specifications

Maximum visibility

- Motorcycle-like performance: up to 60 metres
- Wide beam: 220 lumens
- Colour temperature: 5500 K
- Light output: 80 lux

Power

- Battery: 4 AA Li-ion batteries

Run-time

- City-Eco mode: 8 hours
- High-power: up to 2 hours

Ease of use

- Application: Day, Night
- Easy installation
- Long life LED technology
- USB charger
- Waterproof aluminium housing

Certification

- German certification: StVZO certification



Issue date 2013-11-25

Version: 4.0.1

12 NC: 9282 202 07814
EAN: 87 27900 35183 5

© 2013 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com