




Philips LED Bike lights
Saferide

60 LUX
dynamo driven
Silver aluminium



BF60L60BBLX1



Feel safe, ride safe

Take control of your safety

Empower yourself on the road with the Saferide LED Bikelight 60 dynamo-driven motorcycle-like performance. With a specially crafted retro reflector and unique housing design.

Easy installation, no maintenance

- Long life LED technology
- 4 min standlight function
- Works with all dynamo's

Extra wide illumination

- Motorcycle performance: up to 50 metres road illumination
- High efficiency reflector
- Foreground illumination
- Glare free beam
- Legally approved according to StZVO in Germany

5x more light

- Powered by 2 new generation High-power Luxeon LEDs (60 lux)
- New generation of high-power Luxeon LEDs

PHILIPS

Saferide
60 LUX dynamo driven, Silver aluminium

Highlights

Powered by 2 Luxeon LEDs



Powered by 2 new generation High-power Luxeon LEDs (60 lux). These high quality LEDs have been designed for the automotive industry and are now available to provide safety for bikers on the road.

New generation of LED



To ensure best visibility, our bikelights come equipped with high-power Luxeon LEDs. These high quality LEDs have been designed for the automotive industry and are now available to provide safety for bikers on the road.

Motorcycle performance




Motorcycle performance: up to 50 metres homogeneous road illumination

Long life LED technology



Long life LED technology

Foreground illumination



Foreground illumination

BF60L60BBLX1

Glare free beam



Glare free beam

High efficiency reflector

High efficiency reflector


Legally approved

Legally approved according to StZVO in Germany

4 min standlight function

4 min standlight function

Works with all dynamo's



Works with all dynamo's

Specifications

Maximum visibility

- Motorcycle-like performance: up to 50 metres
- Wide beam: 110 lumens
- Colour temperature: 5500 K
- Light output: 60 lux

Power

- Dynamo: Rotary and hub dynamo

Run-time

- stand light-function: 4 minutes

Ease of use

- 4 min standlight function
- Application: Day, Night
- Easy installation
- Long life LED technology
- Waterproof aluminium housing
- Works with all types of dynamo

Certification

- German certification: StVZO certification



Issue date 2014-02-19

Version: 2.0.1

12 NC: 8670 000 85424
EAN: 87 27900 35055 5

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com