

PHILIPS

Curler

StyleCare Essential

16 mm barrel

200°C temperature

Ceramic coating



BHB862/00



All you need for bouncy curls

Gorgeous curls have never been easier. Simply wrap and style to achieve the curly look you always wanted. The ceramic coating adds shine and gloss to the hair, leaving it bouncy, glamorous and full of life.

Beautifully styled hair

- 16 mm curling barrel for bouncy curls and ringlets
- 200°C high temperature for optimal results

Less hair damage

- Protective ceramic coating for extra-gentle styling

Ease of use

- Blinking LED light indicates when the device is ready to use
- Cool tip for easier and safer use
- Fast heat-up time, ready to use in 60 sec
- 1.8 m power cord
- Swivel cord to prevent tangled wires
- 2-year worldwide guarantee



asimpleswitch.com

Highlights

Vivid, bouncy curls



With the barrel diameter of 16 mm, you can create bouncy curls and ringlets that are full of life, giving you a fun-looking and youthful style.

Gentle on your hair



Protective ceramic coating ensures even heat distribution and less hair damage for shiny and soft hair.

200°C high temperature



200°C high temperature guarantees optimal results, while minimising hair damage.

Ready-to-use indicator



The LED light stops blinking when the curler has heated up and is ready to use.

Cool tip



The tip of the styler is made from a special heat insulating material to keep it cool; you can safely hold it while you're styling for optimal ease of use.

Fast heat-up time



This styler has a fast heat up time and is ready to use in 60 seconds.

1.8 m cord



Convenient to use thanks to the 1.8-m power cord length.

Swivel cord



Useful swivel cord technology rotates the cord to prevent tangled wires.

2-year guarantee



Philips offers a full 2-year guarantee for this product to ensure you have a product with a long lifetime to use every day.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Features

Coating of heated parts: Ceramic
Ready-to-use indicator
Swivel cord
Barrel diameter: 16 mm

Hair type

End result: Tight curls and ringlets
Hair length: Long, Medium

Technical specifications

Styling temperature: 200°C
Number of heat settings: 1
Cable length: 1.8 m
Heat-up time: 60 sec
Voltage: Worldwide V

Service

2-year worldwide guarantee

