

PHILIPS


Curler

StyleCare Essential

16 mm barrel

200°C temperature

Ceramic coating



BHB862/03



All you need for bouncy curls

Gorgeous curls have never been easier. Simply wrap and style to achieve the curly look you always wanted. The ceramic coating adds shine and gloss to the hair, leaving it bouncy, glamorous and full of life.

Beautifully styled hair

- 16mm curling barrel for bouncy curls and ringlets
- 200°C high heat temperature for optimal results

Less hair damage

- Protective ceramic coating for extra gentle styling

Ease of use

- Blinking LED light indicates when the device is ready to use
- Cool tip for easier and safer use
- Fast heat up time, ready to use in 60 sec
- 1.8 m power cord
- Swivel cord to prevent tangled wires
- 2 years of world wide guarantee

Highlights

Vivid, bouncy curls



With the barrel diameter of 16 mm barrel you can create bouncy, full of life curls and ringlets for joyful and young look.

Ready to use indicator



The LED light stops blinking when the curler has heated up and is ready to use.

1.8 m cord



Convenient to use thanks to the 1.8m power cord length.

Gentle on your hair



Protective ceramic coating ensures even heat distribution and less hair damage for shiny and soft hair.

Cool tip



The tip of the styler is made from a special heat insulating material to keep it cool; you can safely hold it while you're styling for optimal ease of use.

Swivel cord



Useful swivel cord technology rotates the cord to prevent tangled wires.

200°C high heat temperature



200°C high heat temperature guarantees optimal results, while minimizing hair damage.

Fast heat up time



This styler has a fast heat up time, being ready to use in 60 seconds.

2 years guarantee



Philips offers a full 2 years guarantee for this product to ensure you have long lifetime product to use every day.

Specifications

Features

Coating of heated parts: Ceramic
Ready to use indicator
Swivel cord
Barrel diameter: 16 mm

Hair type

End result: Tight curls and ringlets
Hair length: Long, Medium

Technical specifications

Styling temperature: 200°C
Number of heat settings: 1
Cable length: 1.8 m
Heat-up time: 60 sec
Voltage: Worldwide V

Service

2-year worldwide guarantee

