

# PHILIPS

## Curler StyleCare

25mm medium barrel

Tourmaline ceramic

Digital temperature settings



BHB864/00



## One wrap away from perfect curls

Easily create perfect, classic curls with our new curler. Tourmaline ceramic coated barrel makes sure your hair is protected, frizz-free and shine with perfection. 200°C high heat allows you to create beautiful curls in one wrap.

### Beautifully styled hair

- Tourmaline ceramic for ultimate smoothness and shine
- Up to 200°C for perfect results
- 25mm medium barrel for classic curls

### Less hair damage

- 8 digital temperature settings for absolute control

### Ease of use

- 30% more styling space on the barrel for long or thick hair
- Cool tip for easier and safer use
- Safety stand for ease of use
- Fast heat up time, ready to use in 60 sec
- Key-lock function to avoid unintentional switching
- Swivel cord to prevent tangled wires
- Auto shut-off for safe usage
- 1.8 m power cord

# Highlights

## Tourmaline ceramic



The smooth ceramic barrel prevents damage to your hair during styling. It is infused with tourmaline to give your curls ultimate smoothness and shine.

## Digital temperature settings

Digital display with 8 temperature settings gives you absolute control to adjust temperature to your hair type for damage prevention.

## Up to 200°C




High temperature enables you to change the shape of your hair and get the curly look you want.

## 25mm medium barrel




25mm medium barrel for classic curls

## 30% more styling space



Increased styling space on the barrel for easier curling even long or thick hair.

## Cool tip



The tip of the styler is made from a special heat insulating material to keep it cool; you can safely hold it while you're styling for optimal ease of use.

## Safety stand



The safety stand enables you to put the curler down safely during use

## Fast heat up time



This styler has a fast heat up time, being ready to use in 60 seconds.

## Key-lock function



You are always in control. No more accidental temperature change with the key-lock function.

## Swivel cord




Useful swivel cord technology rotates the cord to prevent tangled wires.

## Auto shut-off



This styler has been equipped with an automatic shut-off feature. This feature has been designed to provide peace of mind. If left on, the appliance will automatically switch off after 60 min.

## 1.8 m cord



Convenient to use thanks to the 1.8m power cord length.

# Specifications

## Technical specifications

Barrel size: 25mm

Barrel coating: Tourmaline Ceramic

Temperature range: 130 °C - 200 °C

Number of heat settings: 8

Type of temperature control: LCD

Heat-up time: 60 sec

Cord length: 1.8 m

Voltage: Worldwide V

## Features

Auto shut-off: after 60 min

Key lock

Resting stand

Swivel cord

## Service

2-year worldwide guarantee

