

PHILIPS

SplitStop Curler

StyleCare

38mm extra large barrel

SplitStop Technology

Keratin infusion

Digital temperature settings



BHB869/03



Put your curls in the spotlight

Up to 95% split free-ends*

Philips SplitStop curler is designed to keep your hair split-free. Thanks to our UniTemp sensor and SplitStop Technology you can create those curls without worry. So hide no more and step into the spotlight!

Beautifully styled hair

- Up to 200°C for perfect results
- 38mm extra large barrel for loose curls

Less split ends

- SplitStop Technology for ultimate split ends prevention
- Keratin infusion for better care
- 8 digital temperature settings for absolute control

Ease of use

- 30% more styling space on the barrel for long or thick hair
- Cool tip for easier and safer use
- Safety stand for ease of use
- Fast heat up time, ready to use in 60 sec
- Key-lock function to avoid unintentional switching
- Swivel cord to prevent tangled wires
- Auto shut-off for safe usage



asimpleswitch.com

Highlights

SplitStop Technology



Our secret to ultimate split ends prevention is the new SplitStop Technology. It is a unique combination of optimized heat performance and minimized friction level to respect the health of your hair from roots to tips. There are no sudden temperature changes which ensures the optimum heat is delivered constantly and evenly along the barrel when you style. The barrel is coated with smooth ceramic to reduce the traction on hair strands. Create perfect curls with healthier ends full of new life.

Keratin infusion



Keratin is the hair's essential ingredient which makes them strong, healthy and gorgeous looking. The ceramic is enriched with keratin to even better take care of your hair.

Digital temperature settings

Digital display with 8 temperature settings gives you absolute control to adjust temperature to your hair type for damage prevention.

Up to 200°C



High temperature enables you to change the shape of your hair and get the curly look you want.

38mm extra large barrel



38mm extra large barrel for loose curls

30% more styling space



Increased styling space on the barrel for easier curling even long or thick hair.

Cool tip



The tip of the styler is made from a special heat insulating material to keep it cool; you can safely hold it while you're styling for optimal ease of use.

Safety stand



The safety stand enables you to put the curler down safely during use

Fast heat up time



This styler has a fast heat up time, being ready to use in 60 seconds.

Key-lock function



You are always in control. No more accidental temperature change with the key-lock function.



[asimpleswitch.com](https://www.asimpleswitch.com)

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Barrel size: 38mm

Barrel coating: Keratin Ceramic

Temperature range: 130 °C - 200 °C

Number of heat settings: 8

Type of temperature control: LCD

Heat-up time: 60 sec

Cord length: 1.8 m

Voltage: Worldwide V

Features

Auto shut-off: after 60 min

Key lock

Resting stand

Swivel cord

Service

2-year worldwide guarantee

