

PHILIPS

Glam Shine Curler

StyleCare

13mm - 25mm conical barrel

Ionic Care

Titanium enriched barrel

Curl Ready Indicator



BHB872



Vibrant curls and waves that shine

Introducing Glam Shine Curler. Our first curler with ionic care and titanium enriched barrel for gorgeously shiny curls and waves. Unique Curl Ready Indicator helps you create consistent curls all around and protects from overheating.

Beautifully styled hair

- Ionic care for shiny, frizz-free hair
- Titanium enriched barrel for perfect results
- Up to 210°C for perfect results

Less hair damage

- Unique Curl Ready Indicator prevents hair overheating
- 9 digital temperature settings for absolute control

Ease of use


- Longer barrel for long or thick hair
- Fast heat up time, ready to use in 45 sec
- Key-lock function to avoid unintentional switching
- Safety stand for ease of use
- Swivel cord to prevent tangled wires
- 1.8 m power cord
- Worldwide voltage for getting the perfect travel companion



asimpleswitch.com

Highlights

Ionic Care



Charged negative ions eliminate static, condition the hair and smooth down the hair cuticles to intensify the hair's shine and glossiness. The result is smooth, frizz-free hair with vibrant shine.

Titanium enriched barrel



Titanium, used professionally, is valued for its robustness and quick heat transfer resulting in better styling performance. The barrel is enriched with titanium for perfect results.

Curl Ready Indicator

Unique Curl Ready Indicator lets you know when your curl is ready by giving a "beep" signal. This innovative feature helps you get beautiful curls and waves while helping prevent hair overheating. You can always style without using it if you prefer other styling times.

Up to 210°C




High temperature enables you to change the shape of your hair and get the curly look you want.

Digital temperature settings

Digital display with 9 temperature settings gives you absolute control to adjust temperature to your hair type for damage prevention.

Longer barrel



This curler has long barrel of 160mm, ideal for curling long or thick hair.

Safety stand



The safety stand enables you to put the curler down safely during use

Fast heat up time



This styler has a fast heat up time, being ready to use in 45 seconds.

Key-lock function



You are always in control. No more accidental temperature change with the key-lock function.

Swivel cord



Useful swivel cord technology rotates the cord to prevent tangled wires.

1.8 m cord



Convenient to use thanks to the 1.8m power cord length.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Barrel size: 13-25mm

Barrel coating: Titanium Ceramic

Temperature range: 130 °C - 210 °C

Number of heat settings: 9

Type of temperature control: LCD

Heat-up time: 45 sec

Cord length: 1.8 m

Voltage: Worldwide V

Features

Auto shut-off: after 60 min

Key lock

Resting stand

Swivel cord

Service

2-year worldwide guarantee

