

PHILIPS

Hairdryer

DryCare Essential

Compact

1600W

3 heat & speed settings

Cool shot



BHD002/00



Compact, powerful and 35% quieter*

Designed by Philips sound experts

This Philips Essential Care dryer gives you the power and care you need and it is designed for quieter* drying, with a 35% sound improvement versus HP4961/22. Now you can enjoy a powerful and comfortable experience.

Easy to use

- Designed for quieter drying
- Compact design for easy handling
- 1.8m cord for maximum flexibility
- Easy storage hook for convenient storage
- Narrow concentrator for focused airflow

Beautifully styled hair

- 1600W for gentle drying
- 3 flexible speed settings for gentle drying
- Cool Shot sets your style
- ThermoProtect temperature setting



asimpleswitch.com

Highlights

Quieter drying



The design of the air inlet grill allows for increased air flow while, the shape and size of the dryer improves flow of the air through the dryer. The result is faster, more effective drying power. The Philips Essential Care 1600W, has a 35% sound improvement versus HP4961/22. Now you can enjoy a powerful and comfortable experience.

Compact design



Compact and ergonomic, this hairdryer benefits from a clever modern design. The result is a dryer that is light and easy to handle yet small enough to store virtually anywhere.

Narrow concentrator



The concentrator focuses the air flow of air for precision styling. Great for touch ups or to set your style.

Easy storage hook



A rubberized hook can be found on the base of the handle. Use to store easily at home or if staying at a hotel.

1.8m cord



1.8m cord.

1600W for gentle drying




This 1600W hairdryer creates the optimum level of airflow and gentle drying power, for beautiful results every day.

ThermoProtect temperature



The ThermoProtect temperature setting provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results in a caring way.

3 flexible speed settings



This hairdryer offers 3 pre-selected speed/heat combinations to make it quick and easy to achieve the perfect style.

Cool Shot sets your style



A must-have professional setting, the Cool Shot provides a burst of cold air. Use after styling to set and finish your style.



[asimpleswitch.com](https://www.asimpleswitch.com)

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Features

Diffuser: No
Dual voltage: No
Foldable handle: No
Hanging loop
Ion conditioning: No
Number of attachments: 1
Travel pouch: No
Ceramic: No
Coolshot
Nozzle / Concentrator

Service

2-year guarantee

Technical specifications

Color/finishing: ABS high gloss and matt
Frequency: 50-60 Hz
Motor: DC Motor
Voltage: 220-240 V
Wattage: 1600 W
Cord length: 1.8 m
Power: 1600 W

Weight & dimensions

A-Box Dimensions: 594 x 343 x 206mm
A-Box Weight: 530g
Product size: 274 x 78 x 174mm
Product weight (excl. pack): 425g
F-Box weight: 120g

