

# PHILIPS

## Hairdryer

EssentialCare

1800W

Cool shot

Diffuser

220-240V



BHD004/03



## Powerful drying with a pleasant\* sound Designed by Philips sound experts

This Philips EssentialCare dryer gives you the power and care you need with a more pleasant sound. Now you can enjoy a powerful and comfortable experience. \*Tested with 75 women in France 2014

### Easy to use

- Designed for a pleasant sound
- Compact design for easy handling
- Narrow concentrator for focused airflow
- Easy storage hook for convenient storage
- 1.8m cord for maximum flexibility

### Beautifully styled hair

- 1800W for perfect drying results
- ThermoProtect temperature setting
- 3 flexible speed settings for gentle drying
- Cool Shot sets your style
- Adds volume, maximizes thickness, curls and bouncy styles

# Highlights

## Pleasant sound




The design of the air inlet grill allows for increased air flow while, the shape and size of the dryer improves flow of the air through the dryer. The result is faster, more effective drying power with a pleasant sound\*. Now you can enjoy a powerful and comfortable experience. \*Tested with 75 women in France 2014.

## Compact design



Compact and ergonomic, this hairdryer benefits from a clever modern design. The result is a dryer that is light and easy to handle yet small enough to store virtually anywhere.

## Narrow concentrator



The concentrator focuses the air flow of air for precision styling. Great for touch ups or to set your style.

## Easy storage hook



A rubberized hook can be found on the base of the handle. Use to store easily at home or if staying at a hotel.

## 1.8m cord



1.8m cord.

## 1800W for perfect drying



This 1800W hairdryer creates the perfect level of airflow and drying power, for beautiful results every day.


## ThermoProtect temperature



The ThermoProtect temperature setting maintains a constant caring drying temperature and gives additional protection from

overheating the hair. With the same powerful airflow, you can achieve great results in the most caring way.

## 3 flexible speed settings



This hairdryer offers 3 pre-selected speed/heat combinations to make it quick and easy to achieve the perfect style.

## Cool Shot sets your style



A must-have professional setting, the Cool Shot provides a burst of cold air. Use after styling to set and finish your style.

## Volume diffuser

The volume diffuser spreads the flow of air across the hair, boosting volume and reducing frizz while drying. For best results, hold the diffuser close to the crown and root area. The diffuser's fine textured pins will add volume, maximize thickness, bounce and help shape curls.

# Specifications

## Technical specifications

Voltage: 220-240 V

Frequency: 50-60 Hz

Wattage: 1800 W

Power: 1800 W

Cord length: 1.8 m

Color/finishing: PC high gloss and matt

Motor: DC Motor

## Features

Hanging loop

Foldable handle: No

Coolshot

Dual voltage: No

Travel pouch: No

Ceramic: No

Ion conditioning: No

Number of attachments: 2

Nozzle / Concentrator

Diffuser

## Service

2-year guarantee

## Weight & dimensions

Product weight (excl. pack): 485g

Product size: 274 x 88 x 179mm

A-Box Dimensions: 594 x 343 x 206mm

A-Box Weight: 600g

F-Box weight: 125g

