

PHILIPS

Hairdryer

EssentialCare

1800W

Cool shot

Diffuser

220V



BHD004/09



Essential Care, for daily drying with volume

This Philips EssentialCare dryer gives you the power and care you need in a compact and beautiful design. It comes with a volume diffuser for boosting volume and reducing frizz while drying your curls.

Easy to use

- Compact design for easy handling
- Narrow concentrator for focused airflow
- Easy storage hook for convenient storage
- 1.8m cord for maximum flexibility

Beautifully styled hair

- 1800W for perfect drying results
- ThermoProtect temperature setting
- 3 flexible speed settings for gentle drying
- Cool Shot sets your style
- Adds volume, maximizes thickness, curls and bouncy styles



asimpleswitch.com

Highlights

Compact design



Compact and ergonomic, this hairdryer benefits from a clever modern design. The result is a dryer that is light and easy to handle yet small enough to store virtually anywhere.

Narrow concentrator



The concentrator focuses the air flow of air for precision styling. Great for touch ups or to set your style.

Easy storage hook



A rubberized hook can be found on the base of the handle. Use to store easily at home or if staying at a hotel.

1.8m cord



1.8m cord.

1800W for perfect drying



This 1800W hairdryer creates the perfect level of airflow and drying power, for beautiful results every day.

ThermoProtect temperature



The ThermoProtect temperature setting maintains a constant caring drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you can achieve great results in the most caring way.

3 flexible speed settings



This hairdryer offers 3 pre-selected speed/heat combinations to make it quick and easy to achieve the perfect style.

Cool Shot sets your style



A must-have professional setting, the Cool Shot provides a burst of cold air. Use after styling to set and finish your style.

Volume diffuser

The volume diffuser spreads the flow of air across the hair, boosting volume and reducing frizz while drying. For best results, hold the diffuser close to the crown and root area. The diffuser's fine textured pins will add volume, maximize thickness, bounce and help shape curls.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Voltage: 220 V

Frequency: 50-60 Hz

Wattage: 1800 W

Power: 1800 W

Cord length: 1.8 m

Color/finishing: PC high gloss and matt

Motor: DC Motor

Features

Hanging loop

Foldable handle: No

Coolshot

Dual voltage: No

Travel pouch: No

Ceramic: No

Ion conditioning: No

Number of attachments: 2

Nozzle / Concentrator

Diffuser

Service

2-year guarantee

Weight & dimensions

Product weight (excl. pack): 485g

Product size: 274 x 88 x 179mm

A-Box Dimensions: 594 x 343 x 206mm

A-Box Weight: 600g

F-Box weight: 125g

