

# PHILIPS

## Hairdryer

### DryCare Essential

Travel

1600W

3 heat & speed settings

Foldable handle



BHD006/00



## Compact, powerful and 20% quieter\*

Designed by Philips sound experts

This Philips Essential Care dryer gives you the power and care you need and it is designed for quieter\* drying, with a 20 % sound improvement versus HP4940. Now you can enjoy a powerful and comfortable experience wherever you go.

#### Beautifully styled hair

- 1600W for gentle drying
- ThermoProtect temperature setting
- 3 flexible speed settings for gentle drying
- Cool Shot sets your style

#### Easy to use

- Designed for quieter drying
- Foldable handle for easy storage
- Dual voltage for worldwide use
- Easy storage hook for convenient storage
- 1.8m cord for maximum flexibility



[asimpleswitch.com](http://asimpleswitch.com)

# Highlights

## 1600W for gentle drying



This 1600W hairdryer creates the optimum level of airflow and gentle drying power, for beautiful results every day.

## ThermoProtect temperature



The ThermoProtect temperature setting provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results in a caring way.

## 3 flexible speed settings



This hairdryer offers 3 pre-selected speed/heat combinations to make it quick and easy to achieve the perfect style.

## Cool Shot sets your style



A must-have professional setting, the Cool Shot provides a burst of cold air. Use after styling to set and finish your style.

## Quieter drying



The design of the air inlet grill allows for increased air flow while, the shape and size of the dryer improves flow of the air through the dryer. The result is faster, more effective drying power. The Philips Essential Care 1600W, has a 20% sound improvement versus HP4940. This way you can dry your hair quietly without compromising on performance.

## Foldable handle



This hairdryer has foldable handle, making it easy to pack, store and take with you anywhere you go.

## Dual voltage



Dual voltage for worldwide use

## Easy storage hook



A rubberized hook can be found on the base of the handle. Use to store easily at home or if staying at a hotel.

## 1.8m cord



1.8m cord.



[asimpleswitch.com](https://www.asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Technical specifications

Frequency: 50-60 Hz

Wattage: 1600 W

Power: 1600 W

Cord length: 1.8 m

Color/finishing: ABS high gloss and matt

Motor: DC Motor

Voltage: 110-127 / 220-240 V

## Features

Hanging loop

Foldable handle

Coolshot

Dual voltage

Travel Pouch included

Ceramic: No

Ion conditioning: No

Number of attachments: 1

Nozzle / Concentrator

Diffuser: No

## Service

2-year guarantee

## Weight & dimensions

Product weight (excl. pack): 450g

Product size: 125 x 80 x 245mm

A-Box Dimensions: 356 x 283 x 273mm

A-Box Weight: 370g

F-Box weight: 85g

