

PHILIPS

Hairdryer

EssentialCare

1800W

Ions

Foldable handle

Worldwide voltage



BHD007/20



Powerful drying with a pleasant* sound on the go

Designed by Philips sound experts

This Philips EssentialCare dryer gives you the power and care you need with a more pleasant sound. Now you can enjoy a powerful and comfortable experience. *Tested with 75 women in France 2014

Easy to use

- 1.8m cord for maximum flexibility
- Dual voltage for worldwide use
- Easy storage hook for convenient storage
- Foldable handle for easy storage
- Designed for a pleasant sound

Beautifully styled hair

- 1800W for perfect drying results
- 3 flexible speed settings for gentle drying
- Cool Shot sets your style
- Ionic conditioning for shiny, frizz-free hair
- ThermoProtect temperature setting

Highlights

1.8m cord

1.8m cord.

1800W for perfect drying

This 1800W hairdryer creates the perfect level of airflow and drying power, for beautiful results every day.

3 flexible speed settings

This hairdryer offers 3 pre-selected speed/heat combinations to make it quick and easy to achieve the perfect style.

Cool Shot sets your style

A must-have professional setting, the Cool Shot provides a burst of cold air. Use after styling to set and finish your style.

Dual voltage

Dual voltage for worldwide use

Easy storage hook



A rubberized hook can be found on the base of the handle. Use to store easily at home or if staying at a hotel.

Ionic conditioning

Give your hair an instant care with ionic conditioning. Charged negative ions eliminate static and conditions the hair to intensify the hair's shine and glossiness. The result is smooth and frizz-free hair that shines beautifully.

ThermoProtect temperature



The ThermoProtect temperature setting provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results in a caring way.

Foldable handle

This hairdryer has foldable handle, making it easy to pack, store and take with you anywhere you go.

Pleasant sound

The design of the air inlet grill allows for increased air flow while, the shape and size of the dryer improves flow of the air through the dryer. The result is faster, more effective drying power with a pleasant sound*. Now you can enjoy a powerful and comfortable experience.
*Tested with 75 women in France 2014.

Specifications

Features

Diffuser: No
Dual voltage
Foldable handle
Hanging loop
Ionic conditioning
Number of attachments: 1
Ceramic: No
Coolshot
Nozzle / Concentrator

Service

2-year guarantee

Technical specifications

Color/finishing: PC high gloss and matt
Frequency: 50-60 Hz
Motor: DC Motor
Wattage: 1800 W
Cord length: 1.8 m
Power: 1800 W
Voltage: 110-127 / 220-240 V

Weight & dimensions

A-Box Dimensions: 356 x 283 x 273mm
A-Box Weight: 370g
Product size: 125 x 80 x 245mm
Product weight (excl. pack): 450g
F-Box weight: 85g

