

PHILIPS

Pro Hairdryer

DryCare

2200W

AC Motor

95 km/h



BHD176/00



Built for performance, designed for style

Philips DryCare Pro AC dryer has a professional AC motor that reaches up to 95km/h of air speed for fast and professional results. Lightweight, the hairdryer is also easier to handle and results in a comfortable drying experience.

Beautifully styled hair

- 2200W of fast, high performance drying power
- 7mm styling concentrator for perfect styling results
- Ionic conditioning for shiny, frizz-free hair
- Volume diffuser enhances volume, for curls and bouncy styles
- Fast drying, powerful AC motor
- Cold shot, a burst of cold air to set your style

Less Hair Damage

- ThermoProtect temperature setting

Easy to use

- Six flexible speed and heat settings for full control
- Light weight



asimpleswitch.com

Highlights

Shine and Condition



Ionic conditioning enables anti-static drying. Charged negative ions eliminate static, condition the hair and smooth down the hair cuticles to intensify the hair's shine and glossiness. The result is smooth and frizz-free hair that shines beautifully.

Light weight



Philips DryCare Pro hairdryer has a lighter and compact design making it more comfortable to use. The handle has an ergonomic design, making it easy to grip and hold.

Cold shot of air



A must-have professional function, the Cold Shot button provides an intense burst of cold air. It is used after styling to set the style.

AC motor



Philips DryCare Pro 2200W has a high performance AC motor developed for the professional market. It generates up to 95km/h of air speed for fast and effective results.

Volume diffuser



The volume diffuser spreads the flow of air across the hair, boosting volume and reducing frizz while drying. For best results, hold the diffuser close to the crown and root area. The diffuser's fine textured pins will add volume, maximize thickness, bounce and help shape curls.

2200W of power



The DryCare Pro hairdryer has a fast, high performance airflow for 2200W of professional drying and styling results.

ThermoProtect temperature



The ThermoProtect temperature setting provides the optimal drying temperature and gives additional protection from overheating the hair. With the same powerful airflow, you will get the best results in a caring way.

Accurate control



Easily set and control the heat and speed settings to create the perfect style. Choose from 3 heat and 2 speed settings for full control and precise drying and styling.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Technical specifications

Voltage: 220 - 240 V
Frequency: 50-60 Hz
Wattage: 2200 W
Power: 2200 W
Cord length: 1.8 m
Motor: AC Motor

Features

Foldable handle: No
Cool shot
Dual voltage: No
Ceramic coating: No
Ion conditioning
Hanging loop
Diffuser

Nozzle / Concentrator

Number of attachments: 2
Travel Pouch included: No

Service

2-year guarantee

