

# PHILIPS

## Dryer

### DryCare Advanced

ThermoBalance sensor

Ionic

2200W



BHD184/00



Active heat protection,  
for 22% more shine\*.

Continuous change of hot and cold airflow provides a pleasant sensation for hair and scalp. The drying power of 2200W and the TurboBoost setting give you the quick powerful drying and styling you need.

#### ThermoBalance Sensor

- ThermoBalance provides active temperature protection

#### Beautifully styled hair

- 2200W of fast, high performance drying power
- Cool Shot sets your style
- 3 heat and 2 speed settings for full control
- Slim airflow concentrator for a perfect brushing
- Massaging diffuser to maximize volume & boosts curls
- Turbo boost for extra fast drying

#### Less hair damage

- Ionic conditioning for shiny, frizz-free hair

#### Easy to use

- Easy storage hook for convenient storage
- 1.8m cord for maximum flexibility



asimpleswitch.com

# Highlights

## ThermoBalance Sensor



ThermoBalance is an innovative Philips technology that provides smart and superior protection to your hair. The sensor diagnoses continuously the heat of air and constantly adjusts temperature for fast and healthy drying. When ThermoBalance Sensor is activated, the LED is on. You may then feel a pleasant and constant temperature changes, preventing the formation of damaging hotspots on your hair. Your hair and scalp are actively and constantly protected from over heating.

## 2200W of power



This 2200W professional hairdryer creates a powerful airflow. The resulting combination of power and speed makes drying and styling your hair quicker and easier.

## Cool Shot sets your style



A must-have professional setting, the Cool Shot provides a burst of cold air. Use after styling to set and finish your style.

## Accurate control



Easily set and control the heat and speed settings to create the perfect style. Choose from 3 heat and 2 speed settings for full control and precise drying and styling

## 11mm narrow concentrator



The slim styling nozzle concentrate the flow of hair through the 11mm opening for precision styling on specific areas. Great for touch ups or to set your style.

## Massaging diffuser



The asymmetric massaging diffuser has a unique asymmetric design that is contoured to the head, making it easier and more intuitive to use. The diffuser spreads the flow of air across the hair, drying hair more healthy, boosting volume and reducing frizz. The rubber pins can be used to massage and stimulate the scalp and improve hair vitality. For best


results, hold close to the crown and root area and let the diffuser's massaging pins add bounce and shape curls.

## Turbo boost



The turbo boost button increases the airflow, to dry your hair even quicker.

## Ionic conditioning



Give your hair an instant care with ionic conditioning. Charged negative ions eliminate static and conditions the hair to intensify the hair's shine and glossiness. The result is smooth and frizz-free hair that shines beautifully.



[asimpleswitch.com](https://www.asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Features

Ceramic coating: No  
Cool Shot  
Diffuser  
Dual voltage: No  
Foldable handle: No  
Hanging loop  
Ion conditioning

Nozzle / Concentrator

Number of attachments: 2  
Travel Pouch included: No

## Service

2-year guarantee

## Technical specifications

Cord length: 1.8 m  
Frequency: 50-60 Hz  
Motor: DC Motor  
Power: 2200 W  
Voltage: 220-240 V  
Wattage: 2200 W

