

PHILIPS

Hair Dryer

3000 Series

1600W

ThermoProtect attachment

3 heat & speed settings



BHD300/13



Powerful drying at a lower temperature with the ThermoProtect attachment

The uniquely-designed ThermoProtect attachment powerfully mixes warm and cool air for everyday care.

Care and protect

- ThermoProtect attachment

Powerful drying

- 1600W of drying power
- Cool air setting to finish your style

Easy to use

- 3 heat and speed settings
- Slim nozzle for touch-ups and detailed styling

Highlights

1600W of drying power



This 1600W hair dryer creates the optimum level of airflow, for beautiful results every day.

ThermoProtect attachment

The uniquely-designed ThermoProtect attachment powerfully mixes warm and cool air for everyday care. It drops the temperature by 10°C while still drying your hair quickly.

3 heat and speed settings



This hairdryer offers 3 preselected heat/speed combinations, making it quick and easy to achieve the perfect style.

Cool air setting



The cool air setting provides a burst of cold air to finish and hold your style.

14 mm styling nozzle



The slim nozzle precisely focuses the air, for quick touch-ups and perfecting small details of your style.

Specifications

Caring technologies

ThermoProtect

Attachments

ThermoProtect attachment

Nozzle: 14 mm

Features

Heat/Speed settings: 3

Settings: Cool air setting

Storage hook

Technical specifications

Wattage: 1600 W

Motor: DC

Voltage: 220-240 V

Cord length: 1.8 m

Service

2-year worldwide warranty

