

PHILIPS

Hair Dryer

3000 Series

1600W

ThermoProtect attachment

3 heat & speed settings



BHD302/30



Powerful drying at a lower temperature with the ThermoProtect attachment

The uniquely-designed ThermoProtect attachment powerfully mixes warm and cool air for everyday care.

Care and protect

- ThermoProtect attachment

Powerful drying

- 1600W of drying power
- Cool air setting to finish your style

Easy to use

- 3 heat and speed settings
- Adds volume, maximizes thickness, curls and bouncy styles

Highlights

1600W of drying power



This 1600W hair dryer creates the optimum level of airflow, for beautiful results every day.

ThermoProtect attachment



The uniquely-designed ThermoProtect attachment powerfully mixes warm and cool air for everyday care. It drops the temperature by 10°C while still drying your hair quickly.

3 heat and speed settings



This hairdryer offers 3 preselected heat/speed combinations, making it quick and easy to achieve the perfect style.

Cool air setting



The cool air setting provides a burst of cold air to finish and hold your style.

Volume diffuser



The volume diffuser spreads the flow of air across the hair, boosting volume and reducing frizz while drying. For best results, hold the diffuser close to the crown and root area. The diffuser's fine textured pins will add volume, maximize thickness, bounce and help shape curls.

Specifications

Caring technologies

ThermoProtect

Attachments

ThermoProtect attachment

Volume diffuser

Features

Heat/Speed settings: 3

Settings: Cool air setting

Storage hook

Technical specifications

Wattage: 1600 W

Motor: DC

Voltage: 220-240 V

Cord length: 1.8 m

Service

2-year worldwide warranty

