

# PHILIPS

## Hair Dryer

### 3000 Series

1600W

ThermoProtect attachment

3 heat & speed settings



BHD308/10



## Powerful drying at a lower temperature with the ThermoProtect attachment

The uniquely-designed ThermoProtect attachment powerfully mixes warm and cool air for everyday care.

#### Care and protect

- ThermoProtect attachment

#### Powerful drying

- 1600W of drying power
- Cool air setting to finish your style

#### Easy to use

- Foldable handle for easy storage
- 3 heat and speed settings
- Slim nozzle for touch-ups and detailed styling

# Highlights

## 1600W of drying power



This 1600W hair dryer creates the optimum level of airflow, for beautiful results every day.

## ThermoProtect attachment



The uniquely-designed ThermoProtect attachment powerfully mixes warm and cool air for everyday care. It drops the temperature by 10°C while still drying your hair quickly.

## Foldable handle



The compact design with foldable handle makes it easy to pack, store and take the hair dryer with you anywhere you go.

## 3 heat and speed settings



This hairdryer offers 3 preselected heat/speed combinations, making it quick and easy to achieve the perfect style.

## Cool air setting



The cool air setting provides a burst of cold air to finish and hold your style.

## 14 mm styling nozzle



The slim nozzle precisely focuses the air, for quick touch-ups and perfecting small details of your style.

# Specifications

## Caring technologies

ThermoProtect

## Attachments

ThermoProtect attachment

Nozzle: 14 mm

## Features

Foldable handle

Heat/Speed settings: 3

Settings: Cool air setting

Storage hook

## Technical specifications

Wattage: 1600 W

Motor: DC

Voltage: 220-240 V

Cord length: 1.8 m

## Service

2-year worldwide warranty

