

PHILIPS

Auto Curler & Heated
straightening brush

StyleCare

Curls in half the time*

Straight hair in 5 minutes**

Caring technologies

Incl. luxury style case



BHH888/03



Long-lasting styles

Fast and easy

The Philips Prestige style set with Auto Curler and Heated straightening brush for long-lasting perfect styles. It comes with a luxurious style case. Create your own style fast and easy: glamorous curls or naturally straight hair.

Long-lasting perfect styles

- Smart curling system for effortless styling
- Smart curl guards follow the flow of your hair
- 27 styling options for any type of curl you want
- Triple bristle design

Easy to use


- Longer curling barrel styles twice as much hair in one go*
- Large paddle-shaped brush
- Including luxury style case

Care for your hair

- Caring technologies
- Argan oil infusion


Highlights

Smart curling system




Glamorous, lasting curls at the touch of a button. The curl boost technology curls every hair strand like a professional stylist. Salon results from the comfort of your own home.

Longer curling barrel



This auto curler has a unique open design with a longer curling barrel. You can now style twice as much hair in each go and be ready in half the time*.

Smart curl guards



Our unique smart curl guards create glamorous and lasting curls. They rotate to follow the flow of your hair, while gently wrapping it around

the curling barrel. Each strand is curled evenly at a controlled temperature, giving you perfect results every time. It really is like having your own personal stylist at home.

27 styling options



From soft waves to bouncy curls. We guarantee that every choice will be a glamorous one. Choose the temperature, time and curl settings to achieve your desired look every time.


Triple bristle design

Triple bristle design gently detangles and straightens while protecting your scalp from heat.

Paddle-shaped brush

The paddle-shaped design to straighten more hair in one go.

Caring technologies



Our MoistureProtect and ThermoProtect technologies protect your hair from overheating by ensuring the optimal temperature. Enjoy your hair's natural shine.

Luxury style case



Our luxury style case is designed to store both devices safely and protected. It is also great for traveling.

Argan oil infusion



The curling barrel and brush bristles are infused with Argan oil for smooth gliding and ultimate shine.

Specifications

Caring technologies

MoistureProtect technology

Technical specifications

Styling temperature: 170 °C - 190 °C - 210 °C

3 curling directions: Right - Alternate - Left

Heat-up time: 30 sec

Timer settings: 8sec - 10sec - 12sec

Cable length: 2 m

Voltage: Universal V

Features

Auto rotation

Rotating directions

Auto shut-off: after 60 min

Swivel cord

Storage hook

Hair type

All hair types

Accessories

Barrel cleaning accessory

Sectioning accessory

Heated straightening brush

Caring technologies: ThermoProtect

Features: 2 temp. settings: 170°C & 220°C,

Paddle-shaped brush, Number of heated

bristles: 111, Auto shut-off after 60 min

Technical specifications: Total number of

bristles: 247, Cord length: 1.8 m, Heater type:

PTC, White LED light indicator, Universal

voltage

Ease of use: Storage hook, Swivel cord

Service

2-year worldwide guarantee

