

# PHILIPS

Advanced wet and  
dry epilator

Satinelle Advanced

Grips hairs 4x shorter than wax

Our widest epilator head yet

Use in or out the shower

Two speed settings for comfort  
in sensitive areas



BRE605/00



## Our fastest epilation, even on the finest of hairs Firmly grips even fine hairs

Our fastest ever epilator has unique ceramic discs that rotate at a greater speed than ever before and firmly grip fine and short hairs. It comes with an extra-wide epilation head that covers more skin with every stroke.

### Exceptional results

- Epilation head in unique ceramic material for better grip
- Extra-wide epilator head

### Easy and effortless use

- First epilator with S-shaped handle
- Cordless wet and dry for use in bath or shower
- Opti-light helps you target and remove even the trickiest hairs.



[asimpleswitch.com](http://asimpleswitch.com)


# Highlights

## Our fastest epilation ever



Our epilator head is unique in being made from a textured ceramic surface that gently extracts even the finest hairs and those 4x shorter than wax can extract. Now with faster disc rotation than ever before (2200 RPM) for our fastest hair removal.

## Extra-wide epilator head



Extra-wide epilator head covers more skin with every stroke for faster hair removal.

## Ergonomic S-shaped handle



The ergonomic S-shaped handle is easy to steer for maximum control and better reach with natural and precise movements, all over your body.

## Cordless wet and dry usage



Designed with an anti-slip grip, ideal for use with water. Enables a more comfortable, gentle experience in your shower or bath. You can use it cordless for best convenience.

## Opti-Light



Opti-light helps you target and remove even the trickiest hairs

# Specifications

## Ease of use

Cordless  
Handle: S-shaped handle  
Wet and dry use  
Opti-light

## Accessories

Pouch: Basic pouch  
Cleaning brush

## Performance

Epilation system: Patented epilation system  
Epilator head: Extra wide  
Epilation discs: Ceramic discs

## Technical specifications

Voltage: 15 V / 5.4 W  
Tweezing action speed 1: 64,000 per minute  
Tweezing action speed 2: 70,400 per minute  
Number of tweezers: 32

## Power

Battery Type: Lithium-ion  
Usage time: up to 40 minutes  
Charging: 1.5-hour charging time  
Quick charge

## Features

Speed settings: 2 settings



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.