

PHILIPS

Wet & Dry epilator

Satinelle Advanced

For legs, underarms and face

Ceramic discs grip fine hairs

S-shaped handle design

+ 2 accessories



BRE615/00



Our fastest epilation even on the finest of hairs

Our fastest ever epilator has unique ceramic discs that rotate at a greater speed than ever before and firmly grip fine and short hairs. Enjoy weeks of satin smooth skin and treat your body areas with tailored hair removal methods.

Exceptional results

- Epilation head of unique ceramic material for better grip
- Extra wide epilator head

Easy and effortless usage

- First epilator with S-shaped handle
- Cordless wet and dry for use in bath or shower
- Opti-light helps you target and remove even trickiest hairs

Personalized body and face care routines

- Facial area and delicate area cap to remove unwanted hairs


Highlights

Our fastest epilation ever



Our epilator head is unique in being made from a textured ceramic surface that gently extract even the finest hairs and those 4x shorter than wax. Now with faster disc rotation than ever before (2200RPM) for our fastest hair removal.

Extra wide epilator head



Extra wide epilator head covers more skin with every stroke for faster hair removal.

Ergonomic S-shaped handle



The ergonomic S-shaped handle is easy to steer for maximum control and better reach with natural and precise movements, all over your body.

Cordless wet and dry usage



Designed with an anti-slip grip, ideal for use with water. Enables a more comfortable, gentle experience in your shower or bath. You can use it cordless for best convenience.

Opti-Light



Opti-light helps you target and remove even trickiest hairs

Facial and delicate area cap



For more gentleness in all different body areas it includes a facial area cap to easily remove unwanted facial hairs and a delicate area cap for hair from underarm and bikini

Specifications

Ease of use

- Cordless
- Handle: S-shape handle
- Wet and dry use
- Opti-light

Accessories

- Facial area cap
- Delicate area cap
- Pouch: Basic pouch
- Cleaning brush

Performance

- Epilation system: Patented epilation system
- Epilator head: Extra wide
- Epilation discs: Ceramic discs

Technical specifications

- Voltage: 15V / 5.4W
- Tweezing action speed 1: 64000 per minute
- Tweezing action speed 2: 70400 per minute
- Number of tweezers: 32

Power

- Battery Type: Lithium-ion
- Usage time: up to 40 minutes
- Charging: 1.5 hour charging time
- Quick charge

Features

- Speed settings: 2 settings

