

PHILIPS

Wet & Dry epilator

Satinelle Advanced

For legs, body and face

Ceramic discs grip fine hairs

S-shaped handle design

+5 accessories



BRE635/00



Our fastest epilation even on the finest of hairs 2 hair removal routines

Our fastest ever epilator has unique ceramic discs that rotate at a greater speed than ever before and firmly grip fine and short hairs. Enjoy weeks of satin smooth skin and treat your body areas with tailored hair removal methods.

Exceptional results

- Epilation head of unique ceramic material for better grip
- Extra wide epilator head

Easy and effortless usage

- First epilator with S-shaped handle
- Cordless wet and dry for use in bath or shower
- Opti-light helps you target and remove even trickiest hairs

Personalized body and face care routines

- Shaving head and trimming comb for a close shave
- Facial area and delicate area cap to remove unwanted hairs
- Includes skin stretcher


Highlights

Our fastest epilation ever



Our epilator head is unique in being made from a textured ceramic surface that gently extract even the finest hairs and those 4x shorter than wax. Now with faster disc rotation than ever before (2200RPM) for our fastest hair removal.

Extra wide epilator head



Extra wide epilator head covers more skin with every stroke for faster hair removal.

Ergonomic S-shaped handle



The ergonomic S-shaped handle is easy to steer for maximum control and better reach with natural and precise movements, all over your body.

Cordless wet and dry usage



Designed with an anti-slip grip, ideal for use with water. Enables a more comfortable, gentle experience in your shower or bath. You can use it cordless for best convenience.

Opti-Light



Opti-light helps you target and remove even trickiest hairs

Shaving head and trimming comb



The shaving head provides a close shave and more gentleness in different body areas. It comes with a trimming comb to style your bikini area.

Facial and delicate area cap



For more gentleness in all different body areas it includes a facial area cap to easily remove unwanted facial hairs and a delicate area cap for hair from underarm and bikini

Skin stretcher



Skin stretcher cap tightens skin during epilation.

Specifications

Ease of use

Cordless
Handle: S-shape handle
Wet and dry use
Opti-light

Accessories

Shaving head
Skin stretcher cap
Facial area cap
Trimming comb
Delicate area cap
Pouch: Basic pouch
Cleaning brush

Performance

Epilation system: Patented epilation system
Epilator head: Extra wide
Epilation discs: Ceramic discs

Technical specifications

Voltage: 15V / 5.4W
Tweezing action speed 1: 64000 per minute
Tweezing action speed 2: 70400 per minute
Number of tweezers: 32

Power

Battery Type: Lithium-ion
Usage time: up to 40 minutes
Charging: 1.5 hour charging time
Quick charge

Features

Speed settings: 2 settings

