

# PHILIPS

Wet & Dry epilator

Epilator Series 8000

For legs and body

Powerful epilation

+ 3 accessories



BRE700/00



## Powerful epilation. Gentle on skin

Smooth skin for up to 4 weeks

Philips Epilator Series 8000 boasts powerful yet gentle epilation so you can achieve smoothness on your both lower legs in as little as 10 minutes. Enjoy benefits beyond just epilation with extra accessories.

### Exceptional results

- Gentle epilation for smooth skin up to 4 weeks
- Extra wide epilator head
- Delicate area cap to remove unwanted hairs
- Optimal contact cap for maximum comfort

### Easy and effortless usage

- Ergonomic S-shaped handle
- Cordless wet and dry for use in bath or shower
- Unique light ensures you don't miss fine hairs
- Pouch included to store everything in one place.

# Highlights

## Powerful and gentle epilation



Philips Epilator Series 8000 boasts powerful yet gentle epilation with its improved tweezers and over 70,000 hair-catching actions per minute. This means you can cover more skin and achieve flawless smoothness for up to 4 weeks. Treat your lower legs in as little as 10 minutes!

## Extra wide epilator head



Extra wide epilator head covers more skin with every stroke for faster hair removal.

## Award-winning design\*



The ergonomic S-shaped handle is easy to steer for maximum control and better reach with natural and precise movements, all over your body.

## Cordless wet and dry usage



Designed with an anti-slip grip, ideal for use with water. Enables a more comfortable, gentle experience in your shower or bath. You can use it cordless for best convenience.

## Opti-light



Unique light ensures you don't miss fine hairs for best epilation results for all body parts.

## Delicate area cap



For extra gentleness in the areas you need it most, a delicate area cap is included to easily remove unwanted hairs from face, underarm and bikini.

## Optimal contact cap



Epilate with ease and experience maximum comfort with the optimal contact cap. It's designed to reduce skin pulling and discomfort by gently stretching the area you're treating, so you don't have to.

## Storage pouch



Attractive pouch so you can store everything in one place.

# Specifications

## Accessories

Delicate area cap  
Optimal contact cap  
Pouch: Basic pouch  
Cleaning brush

## Performance

Epilator head: Extra wide  
Epilation discs: Ceramic discs

## Ease of use

Wet and dry use  
Cordless  
Opti-light  
Handle: S-shape handle

## Technical specifications

Voltage: 15V / 5.4W  
Tweezing action speed 1: 64000 per minute  
Tweezing action speed 2: 70400 per minute  
Number of tweezers: 32

## Features

Speed settings: 2 settings

## Power

Battery Type: Lithium-ion  
Usage time: up to 40 minutes  
Charging: 2 hours charge  
Quick charge

