

PHILIPS

Beard trimmer

Beardtrimmer series
1000

Stainless steel blades

DuraPower, 30min cordless use

USB charging

2 stubble and beard combs



BT1210/15



Durable consistent performance with DuraPower Self-sharpening stainless steel blades

The DuraPower technology ensures a long-lasting battery performance, while the self-sharpening stainless steel blades trim consistently as on day 1. This trimmer can also be charged with a micro-USB cable and runs for up to 30 minutes.

Trimming performance

- Get a perfect but protective trim
- Choose 5mm long beard, short 3-day stubble or zero trim look
- Skin-friendly blades for smooth skin

Easy to use

- Longer lasting battery
- Up to 30 minutes of cordless use after 8 hours charging
- USB charging for convenient use
- Know when it's time to charge
- Travel lock prevents trimmer from accidentally starting
- Simple maintenance
- Easy to grip

Built to last

- 2-year guarantee, worldwide voltage, no oil needed

Highlights

Self-sharpening blades



The self-sharpening steel blades on the Philips 3000 beard trimmer stay as sharp and effective as on day 1 to deliver a perfect yet protective trim, time after time.

DuraPower technology



This beard trimmer uses DuraPower technology to reduce friction on the blades, preserve the motor, and keep your battery going four times longer.

30 min cordless use



Charge your trimmer for 8 hours with your USB cable to get 30 minutes of cordless use.

USB charging



This beard trimmer comes with a USB cable for more flexible charging via your computer or any USB adaptor. The adaptor is not included (recommended adaptor Philips HQ80).

Choose any of the 3 looks



Use the 5mm comb to trim your long beard, the 1mm comb to create a 3-day stubble look or use your trimmer without a comb to have a zero trim.

Battery indicator



The green light on the adaptor lets you know when your device is charging.

Skin-friendly blades



Designed to prevent scratches and irritation, the blades have rounded tips for smoother skin contact.

Travel lock



The travel lock on the on/off button prevents the appliance from being switched on by accident.

Easy to clean



Detach the head of your Philips beard trimmer and rinse it under the tap for easy cleaning. Then dry it before you put it back on the appliance.

Specifications

Cutting system

Precision (size of steps): By 1mm

Cutter width: 32 mm

Cutting element: Stainless steel blades

Non-scratching teeth: For more comfort

Accessories

Comb: 1 beard comb (5mm), 1 stubble comb (1mm)

Maintenance: Cleaning brush

Power

DuraPower technology: 4x longer battery life

Run time: 30 minutes

Charging: USB charging, 8 hours full charge

Battery Type: NiMH

Automatic voltage: 100-240 V

Adaptor: Not included

Ease of use

Display: Charging indicator

Cleaning: Rinseable attachments

Operation: Cordless use

Travel lock

Design

Handle: Ergonomic Easy Grip

Service

2year guarantee

No oil needed

