

PHILIPS

Beard trimmer

Beardtrimmer series
1000

Stainless steel blades

DuraPower, 30min cordless use

USB charging

3 stubble and beard combs



BT1210/16



Durable consistent performance with DuraPower Self-sharpening stainless steel blades

The DuraPower technology ensures a long-lasting battery performance, while the self-sharpening stainless steel blades trim consistently as on day 1. This trimmer can also be charged with a micro-USB cable and runs for up to 30 minutes.

Trimming performance

- Get a perfect but protective trim
- Skin-friendly blades for smooth skin
- Choose 5mm long beard, short 3-day stubble or zero trim look

Easy to use

- Longer lasting battery
- Up to 30 minutes of cordless use after 8 hours charging
- USB charging for convenient use
- Know when it's time to charge
- Simple maintenance
- Easy to grip
- Travel lock prevents trimmer from accidentally starting

Built to last

- Warranty for purchase protection

Highlights

DuraPower technology



This beard trimmer uses DuraPower technology to reduce friction on the blades, preserve the motor, and keep your battery going four times longer.

Self-sharpening blades



The self-sharpening steel blades on the Philips 3000 beard trimmer stay as sharp and effective as on day 1 to deliver a perfect yet protective trim, time after time.

Skin-friendly blades




Designed to prevent scratches and irritation, the blades have rounded tips for smoother skin contact.

USB charging



This beard trimmer comes with a USB cable for more flexible charging via your computer or any USB adaptor. The adaptor is not included (recommended adaptor Philips HQ80).

30 min cordless use



Charge your trimmer for 8 hours with your USB cable to get 30 minutes of cordless use.

Battery indicator



The green light on the adaptor lets you know when your device is charging.

Ergonomic design



A fast trimmer that's comfortable to hold and use. So you can handle those hard-to-reach areas more easily.

Easy to clean



Detach the head of your Philips beard trimmer and rinse it under the tap for easy cleaning. Then dry it before you put it back on the appliance.

Travel lock



The travel lock on the on/off button prevents the appliance from being switched on by accident.

Built to last



All of our grooming products are built to last. They come with a 2 year warranty, never need to be oiled and are compatible with any voltage worldwide.

Specifications

Cutting system

Cutting element: Stainless steel blades

Precision (size of steps): By 1mm

Cutter width: 32 mm

Non-scratching teeth: For more comfort

Ease of use

Display: Charging indicator

Operation: Cordless use

Cleaning: Rinseable attachments

Travel lock

Design

Handle: Ergonomic Easy Grip

Power

DuraPower technology: 4x longer battery life

Battery Type: NiMH

Run time: 30 minutes

Charging: USB charging, 8 hours full charge

Automatic voltage: 100-240 V

Adaptor: Not included

Service

No oil needed

2-year worldwide guarantee

Accessories

Comb: 1 stubble comb (1mm), 2 beard combs (3, 5 mm)

Maintenance: Cleaning brush

