

# PHILIPS

Beard trimmer

Beardtrimmer series  
1000

Stainless steel blades

DuraPower, 30min cordless use

USB charging

2 stubble and beard combs



BT1230/15



## Trims beard, guards skin

### Protects against nicks and cuts

The DuraPower technology ensures a long-lasting battery performance, while the self-sharpening stainless steel blades trim consistently as on day 1. This trimmer can also be charged with a micro-USB cable and runs for up to 30 minutes.

#### Trimming performance

- Get a perfect but protective trim
- Choose 5mm long beard, short 3-day stubble or zero trim look
- Skin-friendly blades for smooth skin

#### Easy to use

- Longer lasting battery
- Up to 30 minutes of cordless use after 8 hours charging
- USB charging for convenient use
- Know when it's time to charge
- Travel lock prevents trimmer from accidentally starting
- Simple maintenance
- Easy to grip

#### Built to last

- Warranty for purchase protection

# Highlights

## DuraPower technology



This beard trimmer uses DuraPower technology to reduce friction on the blades, preserve the motor, and keep your battery going four times longer.

## Self-sharpening blades



The self-sharpening steel blades on the Philips 3000 beard trimmer stay as sharp and effective as on day 1 to deliver a perfect yet protective trim, time after time.

## 30 min cordless use



Charge your trimmer for 8 hours with your USB cable to get 30 minutes of cordless use.

## USB charging



This beard trimmer comes with a USB cable for more flexible charging via your computer or any USB adaptor. The adaptor is not included (recommended adaptor Philips HQ80).

## Choose any of the 3 looks



Use the 5mm comb to trim your long beard, the 1mm comb to create a 3-day stubble look or use your trimmer without a comb to have a zero trim.

## Battery indicator



The green light on the adaptor lets you know when your device is charging.

## Skin-friendly blades



Designed to prevent scratches and irritation, the blades have rounded tips for smoother skin contact.

## Travel lock



The travel lock on the on/off button prevents the appliance from being switched on by accident.

## Easy to clean



Detach the head of your Philips beard trimmer and rinse it under the tap for easy cleaning. Then dry it before you put it back on the appliance.

# Specifications

## Cutting system

**Cutting element:** Stainless steel blades

**Precision (size of steps):** By 1mm

**Cutter width:** 32 mm

**Non-scratching teeth:** For more comfort

## Ease of use

**Display:** Charging indicator

**Operation:** Cordless use

**Cleaning:** Rinseable attachments

**Travel lock**

## Design

**Handle:** Ergonomic Easy Grip

## Power

**DuraPower technology:** 4x longer battery life

**Battery Type:** NiMH

**Run time:** 30 minutes

**Charging:** USB charging, 8 hours full charge

**Automatic voltage:** 100-240 V

**Adaptor:** Not included

## Service

**2-year warranty**

**No oil needed**

## Accessories

**Comb:** 1 stubble comb (1mm), 1 beard comb (5mm)

**Maintenance:** Cleaning brush

