

PHILIPS

beard trimmer

Beardtrimmer series
3000

1mm precision settings

Stainless steel blades

Efficient corded use



BT3200/15



Pro Skin Advanced Trimmer

The most convenient way to trim your stubble

Style your beard the way you want with this beard trimmer. Precision from as short as 1mm up to 10mm.

Precision

- Easy to select and lock-in length settings, 1-10mm
- 1mm precision

Skin friendly performance

- Skin-friendly rounded tips for smooth skin contact

Easy to use

- Ergonomic design for easier handling
- Efficient power system for corded use
- 2 year guarantee, worldwide voltage, no oil needed

Highlights

10 lock-in length settings



Turn the wheel to simply select and lock-in the length settings you want: from a short beard of 1mm up to a full beard of 10mm, in precise 1mm steps.

Perfect beard every day



Set the trimmer at the lowest position for a perfect 3-day beard, just 1mm long.

Skin-friendly high-performance



Blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent irritation.

Efficient Corded Use



Power cord provides constant power.

Ergonomic design



Easy to hold and use, it's designed to help you trim those hard-to-reach areas.

Built to last



All of our grooming products are built to last. They come with a 2 year worldwide guarantee, worldwide voltage compatibility, and they never need to be oiled.

Specifications

Cutting system

Cutter width: 32 mm

Number of length settings: 10

Precision (size of steps): by 1 mm

Comb type: Stubble

Cutting element: Stainless steel blades

Non-scratching teeth: For more comfort

Range of length settings: 1 up to 10 mm

Accessories

Cleaning brush

Ease of use

Secured length settings

Zoomring: Easily adjust length settings

Operation: Corded only

Design

Handle: Easy grip

Power system

Worldwide voltage: 100–240 V

Create the look you want

Style: Short beard

Service

2-year worldwide guarantee