



Beard & stubble trimmer, Series 3000

- DualCut blades
- 10 adjustable length settings
- 90 min cordless use/8h charge
- Lift&Trim system

BT3210/41

## DualCut blades

For a fast and even trim

The Beard Trimmer 3000 features DualCut blades, for a fast and even trim. Spin the zoom wheel to lock in length settings at 3/64" (1mm) increments. Powered by a Lithium Ion battery for 90 minutes of cordless use.

### Benefits

#### Fast and easy trim

- DualCut blades for a fast and even trim
- 10 adjustable length settings lock in 3/64" (1mm) increments
- Lift&Trim comb captures more low-lying hairs with every pass
- Skin-friendly blades for smooth skin

#### Easy to use

- Lithium Ion battery, for up to 90 minutes of cordless use
- Lights indicate when battery is low, empty, full or charging

- Detachable head for easy cleaning
- Ergonomic design for easier handling
- Travel and storage pouch

#### Built to last

- 2 year warranty, worldwide voltage and no need to oil

**PHILIPS**

# Beardtrimmer 3000

## Features

### DualCut blades



2x more steel blades, for a fast and even trim. Blades are self-sharpening, for durable performance.

### Skin-friendly blades



Blades have rounded tips, for smooth contact with skin. This helps prevent scratching and irritation.

### 10 adjustable length settings



Spin the zoom wheel to lock in length settings at 3/64" (1mm) increments.

### Easy to clean



Detach the head and rinse it under the tap for easy cleaning. Dry it before you put it back on the appliance.

### 90 min cordless use



Powered by a Lithium Ion battery, for up to 90 minutes of cordless use with an 8-hour charge.

### Ergonomic design



Easy to hold and use. Designed to help you trim those hard-to-reach areas.

### Lift&Trim system



Trim your stubble beard with our new Lift&Trim system: the comb lifts and captures more flat-lying hairs with every pass for an even trim.

### Built to last



We back this Philips trimmer with a 2-year warranty: our grooming products are built to last. You'll never need to oil it, and it's compatible with all worldwide voltages.

### Battery indicators



The device features lights which indicate when the battery is low, empty, full or charging. This ensures you don't run out of a charge mid-trim.

### Travel and storage pouch



The travel pouch protects your product during traveling and storage.

## Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

### Cutting system

Precision (size of steps) By 1mm (3/64")

Range of length settings 0.5 up to 10 mm  
Cutting element DualCut blades  
Stainless steel blades Yes

data subject to change  
2019, May 23

## Beardtrimmer 3000

Non-scratching teeth For more comfort

### Create the look you want

Number of length settings 10 integrated length settings

### Accessories

Comb Lift & Trim system  
Pouch Storage pouch  
Maintenance Cleaning brush

### Power

Run time 90 minutes  
Charging 8 hours full charge  
Battery Type Lithium-ion  
Automatic voltage 100-240 V

### Ease of use

Zoom wheel Easily adjust length settings  
Display Battery low indicator  
Charging indicator  
Battery empty indicator  
Cleaning Rinseable attachments  
Operation Cordless use

### Design

Handle Ergonomic Easy Grip

### Service

2-year warranty Yes  
No oil needed Yes



data subject to change  
2019, May 23

Version: 1.6.1  
UPC: 00075020069894

© 2019 Koninklijke Philips N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

[www.philips.com](http://www.philips.com)