

PHILIPS

beard trimmer

Beardtrimmer series
1000

0.5-mm steps, 20 length
settings

35 mins' cordless use/10 hr
charge



BT405/13



Trim fast, look sharp

Style your beard exactly how you want it with this precision beard trimmer. Trim as short as 0.5 mm up to 10 mm.

Precision

- Easily select and lock in length settings, from 0.5 mm to 10 mm

Skin-friendly performance

- Skin-friendly rounded tips for smooth skin

Easy to use

- 35 minutes' battery use after 10 hours of charging
- Light on the adaptor indicates when the battery is charging
- Detachable head for easy cleaning
- Ergonomic design for easier handling
- 2-year guarantee, worldwide voltage, no oiling needed


Highlights

20 lock-in length settings



Turn the wheel to select and lock-in the length setting you want: from a 3-day beard of 0.5 mm up to a full beard of 10 mm, in precise 0.5-mm increments.

Skin-friendly high-performance



Blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent irritation.

Cordless use

NiMH
35 minutes

Up to 35 minutes of cordless power after 10 hours of charging.

Charging indication

The light on the adaptor is green when charging.

Easy to clean

Detach the head and rinse it under the tap for easy cleaning. Dry before you putting it back on the appliance.

Ergonomic design



Easy to hold and use, the precision trimmer is designed to help you style even the most hard-to-reach areas.

Built to last



All of our grooming products are built to last. They come with a 2-year worldwide guarantee and worldwide voltage compatibility, and they never need to be oiled.

Specifications

Cutting system

Cutter width: 32 mm
Precision (size of steps): By 0.5 mm
Range of length settings: 0.5 mm up to 10 mm

Create the look you want

Styles: Short beard, Stubbled look
Styling tools: Stubble comb
Number of length settings: 20 integrated length settings

Accessories

Maintenance: Cleaning brush

Ease of use

Secured length settings
Zoom wheel: Easily adjust length settings
Cleaning: Rinseable attachments
Operation: Cordless use

Design

Handle: Easy grip

Power

Automatic voltage: 100-240 V
Run time: 35 minutes
Charging: 10 hours full charge

Service

2-year worldwide guarantee

