

# PHILIPS

Beard & stubble trimmer  
with full metal blades

Beardtrimmer series  
5000

17 settings - 0.2 mm precision

Lift & trim system guides hair

60 min cordless use/1 hr charge

Wet & dry use



BT5200/13



## Effortless even trim

### Dynamic beard guide system for an even result

This trimmer with full metal blades lets you achieve exactly the 3-day stubble, short beard or long beard look you want. Our new integrated hair lift comb raises hairs for efficient one-pass, even trimming results

#### Effortless trimming

- Lifts the hair up to the level of the blade for even results
- Guides the hairs to the cutter for effortless trimming
- Blades are sharpened twice for faster trimming\*

#### Skin-friendly performance

- Skin-friendly, high-performance blades for the perfect trim

#### Perfect 3-day stubble

- Keep perfect 3 day stubble by using the 0.4 mm setting daily

#### Easy to use

- 17 Lock-in length settings, 0.4–10 mm with 0.2 mm precision
- 60 minutes runtime after a 1 hour charge, or plug it in
- Easy but thorough cleaning
- 2-year guarantee, worldwide voltage and no need to oil



reddot award 2016  
winner


# Highlights

## Dynamic Beard Guide System



The Dynamic Beard Guide system with the help of the integrated hair lift comb lifts the hairs up to the level of the blades for even trimming results and lets you achieve exactly the 3 day stubble, short beard or long beard look you want.

## Integrated Hair lift comb



Trim your stubble in one quick pass, while being gentle on your skin. Our new Integrated hair lift comb lifts and guides the hairs to the level of the blades for effortless, even trimming.

## Full metal blades



This trimmer comes with twice-sharpened full metal blades that cut more hairs in every pass for faster trimming.

## 17 lock-in length settings



Select your preferred trim length by simply turning the zoom wheel on the handle until the length you want is displayed from 0.4–10 mm with 0.2 mm precision. Your chosen length is now "locked in" for a perfectly even trim.

## Corded and cordless use



60 minutes

Charge your beard trimmer for 1 hour to get 60 minutes of cordless use. If you need more energy while trimming, you can simply plug the trimmer into the wall. This trimmer has been designed to work both cordlessly and while plugged in.

## 100% waterproof



The 100% waterproof beard trimmer, simply rinse it under the tap for a thorough, easy clean.

## Skin-friendly blades



Get a perfect yet protective trim, time after time. The beard trimmer's steel blades lightly brush against one another, sharpening themselves as they trim so they stay extra sharp and effective. They also have rounded tips and combs to help prevent skin irritation.



## iF DESIGN AWARD 2016

Beard trimmer series 5000iF DESIGN AWARD 2016



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



reddot award 2016  
winner

## Red Dot Award 2016: Winner

Beard trimmer series 5000Red Dot Award 2016: Winner

# Specifications

## Cutting system

**Precision (size of steps):** From 0.2 mm  
**Cutting element:** Stainless steel blades  
**Non-scratch teeth:** For more comfort

## Create the look you want

**Number of length settings:** 17 integrated length settings

## Accessories

**Comb:** Integrated hair lift comb  
**Maintenance:** Cleaning brush

## Ease of use

**Cleaning:** Fully washable  
**Zoom wheel:** Easily adjust length settings  
**Display:** Battery light  
**Operation:** Corded and Cordless use

## Design

**Colour:** Black

## Power

**Run time:** 60 minutes  
**Charging:** 1 hour full charge  
**Automatic voltage:** 100–240 V

## Service

**2 year guarantee**  
**No oil needed**

