

PHILIPS

Stubble trimmer

Beardtrimmer series
5000

0.2 mm precision settings

Full metal blades

70 min cordless use/1 hr charge

Integrated hair lift comb



BT5205/83



Effortless even trim

Dynamic beard guide system for an even result

This trimmer with full metal blades lets you achieve exactly the 3-day stubble, short beard or long beard look you want. Our new integrated hair lift comb raises hairs for efficient one-pass, even trimming results

Effortless trimming

- Lifts the hair up to the level of the blade for even results
- Guides the hairs to the cutter for effortless trimming
- Blades are sharpened twice for faster trimming*

Perfect 3-day stubble

- Keep perfect 3 day stubble by using the 0.4 mm setting daily

Easy to use

- 17 Lock-in length settings, 0.4-7 mm with 0.2 mm precision
- 70 minutes runtime after a 1 hour charge, or plug it in
- 100% waterproof for easy, thorough cleaning
- 2-year guarantee, worldwide voltage and no need to oil

Shape, edge, define your facial style

- 3 precision combs for an even trim of facial hair
- Detail trimmer for perfect facial details
- Detail shaver for perfect lines and contours


Highlights

Dynamic Beard Guide System



The Dynamic Beard Guide system with the help of the integrated hair lift comb lifts the hairs up to the level of the blades for even trimming results and lets you achieve exactly the 3 day stubble, short beard or long beard look you want.

Integrated Hair lift comb



Trim your stubble in one quick pass, while being gentle on your skin. Our new Integrated hair lift comb lifts and guides the hairs to the level of the blades for effortless, even trimming.

Full metal blades



This trimmer comes with twice-sharpened full metal blades that cut more hairs in every pass for faster trimming.

17 lock-in length settings



Select your preferred trim length by simply turning the zoom wheel on the handle until the length you want is displayed from 0.4-7 mm with 0.2 mm precision. Your chosen length is now "locked in" for a perfectly even trim.

Corded and cordless use

Li-Ion
70 minutes

Charge your beard trimmer for 1 hour to get 70 minutes of cordless use. If you need more energy while trimming, you can simply plug the trimmer into the wall. This trimmer has been designed to run both cordless and plugged in.

100% waterproof



Simply rinse your waterproof beard trimmer under the tap to thoroughly clean it.

Ideal stubble setting



Keep an ideal 3 day stubble, day after day, by using the trimmer's shortest 0.4 mm setting.

Built to last



We back this Philips trimmer with a 2 year guarantee: our grooming products are built to last. You'll never need to oil it, and it's compatible with all worldwide voltages.

3 precision combs



Trim and maintain the uniform length of your stubble, beard, goatee, sideburns and moustache with the 1-mm, 3-mm and 5-mm click-on precision combs.

Specifications

Cutting system

Precision (size of steps): From 0.2 mm

Cutting element: Stainless steel blades

Non-scratch teeth: For more comfort

3 precision beard combs: 1, 3, 5 mm (1/32", 1/8", 3/16")

Precision beard trimmer: 21 mm (13/16")

Create the look you want

Number of length settings: 17 integrated length settings

Accessories

Comb: Integrated hair lift comb

Maintenance: Cleaning brush

Ease of use

Cleaning: Fully washable

Zoom wheel: Easily adjust length settings

Display: Battery light

Operation: Corded and Cordless use

Design

Finishing: Chrome finish

Handle: Soft touch handle

Power

Run time: 70 minutes

Charging: 1 hour full charge

Automatic voltage: 100–240 V

Service

2 year guarantee

No oil needed

