

PHILIPS

NORELCO

Beard & Head trimmer Series 5100

0.2mm precision settings

Stainless steel blades

70 min cordless use/1h charge

3 combs for beard and hair



BT5210/42



Even length at every angle

Engineered for an effortless even trim

This beard & head trimmer helps you to achieve exactly the 3-day stubble, short or long beard look or hair style you want. The new hair lift comb lifts & guides hairs to the blade for efficient one pass trimming.

Effortless trimming

- Lifts the hair up to the blade for an even result
- Blades are double sharpened for faster trimming*
- Guides the hairs to the cutter for effortless trimming
- Includes 2 combs for short & long hair (0,4-13mm)

Perfect 3 day stubble

- Keep perfect 3-day stubble by using the 0.4mm setting daily

Skin-friendly performance

- Skin-friendly, high-performance blades for the perfect trim

Easy to use

- Select your lengths from 1/64"-1/2" with the zoom wheel
- 70 minutes runtime after a 1 hour charge, or plug it in
- Fully washable for easy, thorough cleaning
- 5 year warranty offer



reddot award 2016
winner


Highlights

Dynamic Beard Guide System



Innovative lift & trim technology effectively lifts and guides hairs for a more efficient cut. Rounded contour comb technology is designed to deliver a skin friendly and more even trim.

Integrated Hair lift comb



Trim your stubble in one quick pass, while being gentle on your skin. Our new Integrated hair lift comb lifts and guides the hairs to the level of the blades for effortless, even trimming.

Self-sharpening steel blades



The blades are designed to effectively cut each hair perfectly, preventing skin irritation. They are double sharpened to cut more hairs in every pass for faster trimming.

Corded and cordless use



Advanced lithium-ion battery delivers maximum power for high performance cutting. Charge your beard trimmer for 1 hour to get 70 minutes of cordless use. It can also be used while charging.

Built-in 17 length settings



Select your preferred trim length by simply turning the zoom wheel until the length you want is displayed from 0,4 - 7mm (1/64" to 9/32") with 0,2mm precision for beard and short hair trimming and 7 - 13mm (9/32" to 1/2") for long hair trimming.

Fully washable



Simply rinse the beard trimmer head under the tap to thoroughly clean it. The trimmer is completely waterproof.



iF DESIGN AWARD 2016

Beardtrimmer series 5000iF DESIGN AWARD 2016



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.



reddot award 2016 winner

Red Dot Award 2016: Winner

Beard trimmer series 5000Red Dot Award 2016: Winner

Specifications

Cutting system

Precision (size of steps): From 0.2mm
Cutting element: Stainless steel blades
Non-scratching teeth: For more comfort

Create the look you want

Number of length settings: 17 integrated length settings

Accessories

Comb: Integrated hair lift comb, Long hair comb, Short hair comb
Maintenance: Cleaning brush

Ease of use

Cleaning: Fully washable
Zoom wheel: Easily adjust length settings
Display: Battery light
Operation: Corded & Cordless use

Design

Finishing: Chrome finish
Handle: Soft touch handle

Power

Run time: 70 minutes
Charging: 1 hour full charge
Automatic voltage: 100-240 V

Service

2-year warranty: Yes, Plus 3-years with registration
No oil needed

