

PHILIPS

waterproof beard
trimmer

Beardtrimmer series
5000

0.2mm precision settings

Full metal dual-sided trimmer

60mins cordless use/1h charge



BT5270/15



Perfect precision

The beard trimmer with as little as 0.2mm steps

Switch easily between trimming and detailing with the dual-sided reversible trimmer. Just 'lock in' the trimmer wheel for the precise length you want: from as short as 0.4mm up to 10mm.

Precision

- Trim from 0.4mm to 10mm in steps as short as 0.2mm
- The zoom wheel 'locks in' your chosen length setting
- Dual-sided trimmer: 32mm and 15mm sides for perfect details
- The 0.4mm stubble setting gives you a 3-day beard every day

Skin-friendly performance

- Skin-friendly, high-performance blades for the perfect trim

Easy to use

- 100% waterproof for easy cleaning
- The beard comb ensures you get a perfectly even trim
- 2 year warranty, worldwide voltage and no need to oil
- 60 minutes cordless use after a 1-hour charge, or plug it in



asimpleswitch.com

Highlights

0.2mm precision



You can adjust the cutting length with great precision to give you exactly the trim you want. The length settings go up in tiny 0.2mm steps between 0.4mm and 1mm, then in 0.5mm steps between 1mm and 5mm, and finally in 1mm steps between 5mm and 10mm - giving you perfect precision with control.

17 lock-in length settings



To select your preferred trim length, just turn the zoom wheel on the handle until the length you want is displayed. Your chosen length is now 'locked in' for a precise and even trim.

Dual-Sided trimmer



Take off the adjustable length comb, and there's a reversible, dual-sided precision trimmer underneath. One side is a 32mm high-performance trimmer. Turn it around, and there's a 15mm-wide precision trimmer - perfect for getting into small spaces, like under

your nose or around your mouth. It's designed to cut very close while still protecting your skin, and its small size and angled design make it easy to see what you are doing for fine lines and details.

Skin-friendly high performance



The steel blades lightly brush against each other, so they sharpen themselves as you trim! The blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent skin irritation.

100% waterproof



To clean the trimmer head, simply rinse it under the tap.

Beard comb



The design of the beard comb gives you more control, allowing you to trim your beard perfectly evenly.

Perfect 3-day beard every day



If you want a perfect 3-day beard, just use the trimmer's shortest setting of 0.4mm. For a perfectly groomed longer beard, simply adjust the setting to the exact length you need.

Built to last



We back this Philips trimmer with a 2-year warranty: our grooming products are built to last. You'll never need to oil it, and it's compatible with all worldwide voltages.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas - Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Accessories

Maintenance: Cleaning brush
Comb

Ease of use

Cleaning: 100% Waterproof
Battery Run time: 1 hour charge 60 mins runtime
Operation: Corded & Cordless use

Precision

Length Settings: 17 Length from 0.4 mm to 10 mm

Power

Automatic voltage: 100-240 V

Service

Guarantee: 2 - Year Worldwide Guarantee

Categorization

Trimmers: BeardTrimmer5000

