

PHILIPS

NORELCO

Wet & dry beard
trimmer, Series 5000

Beardtrimmer 5100

0.2mm precision settings

Full metal dual-sided trimmer

60mins cordless use/1h charge



BT5275/41



Perfect precision

Maximum precision for any look

Easily switch between trimming and detailing with the dual-sided reversible trimmer. Enjoy maximum precision from lengths as short as 1/64" (0.4mm) and up to 13/32" (10mm).

Precision

- Trim with precision from 1/64" to 13/32" (0.4mm to 10mm)
- The zoom wheel 'locks in' your chosen length setting
- Dual-sided reversible trimmer for ultimate precision
- Set length to 1/64" (0.4mm) for perfect stubble every day

Skin-friendly performance

- Skin-friendly, high-performance blades for the perfect trim

Easy to use

- Water-resistant for easy cleaning
- The beard comb ensures you get a perfectly even trim
- 2 year warranty, worldwide voltage and no need to oil
- 60 minutes cordless use after a 1-hour charge, or plug it in



asimpleswitch.com

Highlights

Perfect precision

With cutting lengths ranging from 1/64" to 13/32" (0.4mm to 10mm), you can get the exact trim you want. The length settings go up in precise 1/127", 1/32", and 3/64" (0.2mm, 0.5mm, and 1mm) steps in between – giving you perfect precision with control.

17 lock-in length settings



To select your preferred trim length, just turn the zoom wheel on the handle until the length you want is displayed. Your chosen length is now 'locked in' for a precise and even trim.

Dual-Sided trimmer



The dual-sided reversible trimmer gives you the versatility to create your unique look. On one side, the 1 17/64" (32mm) high-performance trimmer cuts very close while protecting your skin. On the other side, the 5/8" (15mm) precision trimmer creates a detailed look, even in those hard-to-reach areas like under the nose and around the mouth. The trimmer's small size and angled design make it easy to see what you are doing for accurate fine lines and details.

Skin-friendly high performance



The steel blades lightly brush against each other, so they sharpen themselves as you trim! The blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent skin irritation.

Water-resistant



To clean, simply rinse the water-resistant trimmer under the tap.

Beard comb



The design of the beard comb gives you more control, allowing you to trim your beard perfectly evenly.

Perfect stubble every day


If you want that perfect stubble look, just use the trimmer's short 1/64" (0.4mm) setting. For a perfectly groomed longer beard, simply adjust the setting to the exact length you need.

Built to last



We back this Philips trimmer with a 2-year warranty: our grooming products are built to last. You'll never need to oil it, and it's compatible with all worldwide voltages.

Rechargeable and corded use



You get 60 minutes of cordless use after a 1-hour charge. If you run out of battery power while trimming, just plug it in and keep trimming.



asimpleswitch.com

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Accessories

Maintenance: Cleaning brush
Comb

Ease of use

Cleaning: 100% Waterproof
Battery Run time: 1 hour charge 60 mins runtime
Operation: Corded & Cordless use

Precision

Length Settings: 17 Length from 0.4 mm to 10 mm

Power

Automatic voltage: 100-240 V

Service

Guarantee: 2 - Year Worldwide Guarantee

Categorization

Trimmers: BeardTrimmer5000

