

PHILIPS

Beard and hair
trimmer

Beardtrimmer series
5000

One pass even trim

40 adjustable lengths

DualCut 2x the steel blades

Lithium-ion 90 minute run time



BT5511/49



One pass even trim

Beard and hair trimmer

The Philips Norelco Beard and Hair Trimmer 5500 is a premium beard and stubble trimmer which also cuts hair. Designed for an even trim from any angle and features 40 adjustable lengths, DualCut steel blades and 90 minutes of lithium-ion run time.

Even trimming results

- Trims evenly and captures low-lying hairs

Cutting performance

- One pass, even trim

Easy to use

- Cordless use for up to 90 mins

Precision and control

- Adjusts to different length settings

Stainless steel blades

- Maximum precision with 2x more blades

Highlights

Specifications

One pass even trim



Never miss a spot again with the Philips Beardtrimmer Series 5000. Our inbuilt Lift&Trim system picks up low-lying hairs and rounded combs trim at an even length.

40 adjustable length settings for beard and hair



Cut to the exact length you're after with this cordless beard trimmer. Just spin the zoom wheel to one of 40 length settings in 1/128" (0.2mm) increments.

DualCut



Get a fast and even trim with Philips beard trimmer for men, with self-sharpening steel blades and 2x as many blades, thanks to DualCut.

Lift & Trim PRO system



Stubble doesn't stand a chance. The Lift&Trim Pro system captures all your low-lying hairs and lifts them up toward the blades for a precise cut – whilst still being an ideal trimmer for long beards too.

90 min corded/cordless use



Don't get tangled up in your stubble trimmer – a 1 hour charge provides up to 90 minutes of cordless grooming time. Or keep it plugged in for uninterrupted trimming. The 5 minute quick charge function gives you enough power for one trim.

2-year warranty



All of our grooming products are built to last. They come with a 2 year warranty, never need to be oiled and are compatible with any voltage worldwide.

Cutting system

Cutting element: DualCut 2x the steel blades
Range of length settings: 0.4mm (1/64") to 20mm (25/32")
Precision (size of steps): From 0.2mm (1/128")

Accessories

Attachments: 3 guards

Ease of use

Operation: Corded & Cordless use

Cleaning: Fully washable

Zoom wheel: Easily adjust length settings

Power

Battery Type: Lithium-ion

Run time: 90 minutes

Automatic voltage: 100-240 V

Service

No oil needed

2-year warranty

