

PHILIPS

Beard and hair
trimmer

Beardtrimmer series
5000

One pass even trim

40 adjustable lengths

DualCut 2x the steel blades

Lithium-ion 90 minute run time



BT5511/49



One pass even trim

Beard and hair trimmer

The Philips Norelco Beard and Hair Trimmer 5500 is a premium beard and stubble trimmer which also cuts hair. Designed for an even trim from any angle and features 40 adjustable lengths, DualCut steel blades and 90 minutes of lithium-ion run time.

Even trimming results

- Guides low-lying hairs towards the blades for an even trim

Cutting performance

- Designed for an even trim from any angle

Easy to use

- Up to 90 min runtime after a 1 hour charge, or plug it in

Precision and control


- Spin the zoom wheel to lock in 40 length settings

Stainless steel blades

- 2x the steel blades

Highlights

One pass even trim



Designed for an even trim from any angle. Lift&Trim system captures low-lying hairs, and rounded combs trim at an even length.

40 adjustable length settings for beard and hair




Spin the zoom wheel to lock in length settings from 1/128"(0.2mm) increments.

DualCut



2x more steel blades, for a fast and even trim. Blades are self-sharpening, for durable performance.

Lift & Trim PRO system



Trim your stubble in one stroke with our innovative Lift & Trim PRO system. It lifts low-lying hairs and guides them towards the sharp metal blades for a precise cut.

90 min corded/cordless use



Charge your beard trimmer for 1 hour to get up to 90 minutes of cordless use, or simply use it plugged into the wall. Otherwise the quick charge function gives you a full trim after just 5 minutes of charging.

2-year warranty



All of our grooming products are built to last. The BT5511 comes with a 2-year warranty.

Specifications

Cutting system

Cutting element: DualCut 2x the steel blades
Range of length settings: 0.4mm (1/64") to 20mm (25/32")
Precision (size of steps): From 0.2mm (1/128")

Accessories

Attachments: 3 guards

Ease of use

Operation: Corded & Cordless use

Cleaning: Fully washable

Zoom wheel: Easily adjust length settings

Power

Battery Type: Lithium-ion

Run time: 90 minutes

Automatic voltage: 100-240 V

Service

No oil needed

2-year warranty

